


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	—		A	INITIAL RELEASE	24NOV2009	RC	AH

D

C

B

A



LC CONN. MARK	SC CONN. MARK
A	B
B	A

NOTES:

- 1
- ATTENUATION $\leq$ 0.3 dB, MEASURED AT 1310 nm
ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
- 2
- RETURN LOSS $\geq$ 45 dB, IN MATED CONDITION
AGAINST REFERENCE CONNECTOR AT 1310 nm
- 3
- TUNED CONNECTORS
- 4


SC DUPLEX CONNECTORS ARE LEFT UNASSEMBLED AS SHOWN
- 5
- CABLE INFORMATION:
 - CORE DIAMETER: 9/125 μ m
 - OUTER JACKET DIAMETER: 1.8x3.6 mm
 - OUTER JACKET COLOUR: YELLOW
 - OUTER JACKET MATERIAL: LSZH
- 6

BLANK LABEL
- 7

INFORMATION ON LABEL
 - BARCODE
 - UNIQUE SERIAL NUMBER
 - TYCO ELECTRONICS PART NUMBER & ORDER NUMBER
 - ATTENUATION & RETURN LOSS AT 1310 nm

STANDARD LENGTHS ACCORDING TO
CUSTOMER DRAWING 1206850

PART NUMBER	"L" (meter)
X-2061312-Y	XY.0

6	FOAC INFORMATION LABEL					5
1	SC CONNECTOR, SM, DUPLEX HOUSING, RET. PLATE HALF, BLUE					4
1	SC CONNECTOR, SM, DUPLEX HOUSING, BEAM HALF, BLUE					3
1	LC DUPLEX CONNECTOR, SINGLE MODE, BLUE					2
L	FOCAB 1.8MZ 9/125, YELLOW, LSZH					1
Qty	Description					Item
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R. COOLEN 16OCT2009	 Tyco Electronics Corporation 's-Hertogenbosch, Nederland		
			CHK A. HENGELMOLEN 16OCT2009			
			APVD A. HENGELMOLEN 16OCT2009			
			PRODUCT SPEC			
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME		
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		FIBER OPTIC LEAD 1.8MZ LC/DPX - SC/DPX SINGLE MODE 9/125		
MATERIAL -		FINISH -		APPLICATION SPEC -		RESTRICTED TO -
			WEIGHT -			
CUSTOMER DRAWING			SIZE A2			CAGE CODE 00779
			DRAWING NO C=2061312			
			SCALE NTS			SHEET 1 of 1
			REV A			