

Rittal – The System.

Faster – better – everywhere.

Cable gland HD – HD 2410.020

Date : Nov 7, 2017

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Cable gland HD – HD 2410.020

created: 07.11.2017 build on www.rittal.com/uk-en



Product description

Design: Standard

Benefits: Smooth, solid exterior surfaces effectively prevent the depositing of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.

Applications: Manufacturer
Clean room technology (e.g. pharmaceuticals)
Biotechnology
Chemical industry

Material: Cap nut: Stainless steel 1.4305 (AISI 303)
Seal: Conforms to FDA 21 CFR 177.2600

**Protection category
IP to IEC 60 529:** IP 68 (5 bar, 30 min)

**Protection category
IP to DIN 40 050-9:** IP 69K

Product features

**Ambient temperature
range:** -20°C...+100°C

Thread: M20 x 1.5

**Operating
temperature (max.):** 100 °C

Cable entry: For cable diameter: 6 mm - 12 mm

Packs of:	5 pc(s).
Weight/pack:	0.35 kg
EAN:	4028177162204
Customs tariff number:	73181900
ETIM 6.0:	EC000441
ETIM 5.0:	EC000441
eCl@ss 8.0/8.1:	27149109
eCl@ss 7.0/7.1:	27189265
eCl@ss 6.0/6.1:	27189265
eCl@ss 5.1/5.1.4:	27180102
Product description (long):	HD Cable gland, stainless steel 1.4305, size: M20x1,5, for cablesØ 6-12 mm, Standard version
Approvals	
Certificates:	DGUV NA
Declarations:	Manufacturer's declaration