

## Classic ECO Ball

CLECO BAL 240V 42W E14 SV1

0023777



### Range features

- 1:1 replacement of Incandescent Ball lamp
- More efficient - more savings
- Excellent colour rendering (CRI = 100)
- Instant illumination
- Sparkling light output
- Less heat generation than incandescent lamp
- Less CO2 emissions
- Identical shape as standard incandescent lamp
- Commercial and domestic application
- 100% dimmable
- Average rated life 2000 hrs - up to two times more average life compared to incandescent lamps



### PRODUCT OVERVIEW

Ordering number	0023777
Light colour	828 Homelight
Technology	Halogen
Energy class	D
Average life (Rated) (h)	2000
Lamp finish	Clear
Lamp shape	Ball
Dimmable	Yes
Cap/Base	E14
Type	Ball ECO
EAN code	5410288237770
CRI (Ra)	100
Beam angle(°)	na
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	625
Watt (Nominal) (W)	42
Equivalent watt (W)	55
Voltage (V)	240

## Classic ECO Ball

CLECO BAL 240V 42W E14 SV1

0023777

### DATA TABLE

#### General data

Ordering number	0023777
Technology	Halogen
Average life (Nominal) (h)	2000
Average life (Rated) (h)	2000
Energy saving lamp	No
Energy class	D
Lamp shape	Ball
Lamp finish	Clear
Dimmable	Yes
Cap/Base	E14
Type	Ball ECO
EAN code	5410288237770
E-number SE	8355968
E-number FI	4740164
Long description	1:1 replacement of Incandescent Ball lamp. More efficient - more savings. Excellent colour rendering (CRI = 100). Instant illumination. Sparkling light output. Less heat generation than incandescent lamp. Less CO2 emissions. Identical shape as standard incandescent lamp. Commercial and domestic application. 100% dimmable. Average rated life 2000 hrs - up to two times more average life compared to incandescent lamps
Product name	CLECO BAL 240V 42W E14 SV1
Lamp mercury content (mg)	0
Starting time (max) (s)	0.01
Warm-up time to 60% of full light (max) (s)	Instant full light
Control gear required	No
Fixture rating	Open
IEC Reference	IEC 60357
IEC Reference 2	IEC 60432-2
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	> 8000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

# Classic ECO Ball

CLECO BAL 240V 42W E14 SV1

**0023777**

## Optical data

<b>Light colour</b>	828 Homelight
<b>CRI (Ra)</b>	100
<b>Suitable for accent lighting</b>	No
<b>Beam angle(°)</b>	na
<b>Colour temperature (K)</b>	2800
<b>Luminous flux (Rated) (lm)</b>	625
<b>Lumen maintenance at end of nominal life (%)</b>	80
<b>Luminous flux (Nominal) (lm)</b>	625

## Electrical data

<b>kWh per 1000 hours burning time</b>	42
<b>Watt (Rated) (W)</b>	42
<b>Watt (Nominal) (W)</b>	42
<b>Equivalent watt (W)</b>	55
<b>Voltage (V)</b>	240
<b>Lamp power factor</b>	1

## Physical data


<b>Weight (kg)</b>	0.02
<b>Lamp Length (mm) - C/L</b>	83
<b>Max. Lamp Diameter (mm) - D</b>	46
<b>Single packaging type</b>	Box/Sleeve
<b>Single package dimensions (L x W x H) (cm)</b>	7.60 x 4.55 x 4.55
<b>Inner package dimensions (L x W x H) (cm)</b>	23.50 x 10.00 x 8.50
<b>Inner package net weight (kg)</b>	0.19
<b>Outer package dimensions (L x W x H) (cm)</b>	52.00 x 25.50 x 19.00

## Classic ECO Ball

CLECO BAL 240V 42W E14 SV1

0023777

### TECHNICAL DRAWINGS



### ENERGY LABEL

