



Product Information

2444DYP200R26-28D

Swivel castor with central, total or directional lock, housing made of pressed steel, zinc-chromatised, covered precision swivel bearing, hardened balls and tracks, bearing sleeve welded to fork, wheel axle with nut.

Wheel centre made of pressed steel, Tread: solid rubber, black, non-staining, electric conductive, with threadguards, precision ball bearing.

Wheel diameter	200 mm
Tread width	32 mm
Hardness of tread	Shore A 80
Bolt-Ø	8 mm
Bolt length	96 mm
Offset	62 mm
Overall height	240 mm
Temperature	-20 / +85 °C
Standard	EN 12530
Dynamic load capacity	100 kg
Static load capacity	200 kg
Hardness of tread	