

F

E

D

C

B

A

F







E

D

C

B

A



注)


NOTES

- 材質
MATERIAL
ハウジング：ガラス入りLCP、白色、UL94V-0
HOUSING:G.F.LCP,WHITE,UL94V-0
ターミナル：銅合金 (t=0.2)
TERMINAL:COPPER ALLOY
吸着カバー：ステンレス (t=0.2)
VACUUM COVER:STAINLESS STEEL
補強金具：銅合金 (t=0.25)
FITTING NAIL:COPPER ALLOY
- メッキ仕様
PLATING
ターミナル：接点部：金メッキ 0.25 マイクロメートル以上
TERMINAL: CONTACT AREA:GOLD 0.25 MICROMETER MINIMUM
半田付け部：錫メッキ 1.0 マイクロメートル以上
SOLDER TAIL AREA:TIN 1.0 MICROMETER MINIMUM
下地メッキ：ニッケルメッキ 1.5 マイクロメートル以上
UNDER-PLATING:NICKEL 1.5 MICROMETER MINIMUM
補強金具：銅メッキ 1.0 マイクロメートル以上
FITTING NAIL: TIN 1.0 MICROMETER MINIMUM
下地メッキ：ニッケルメッキ 1.0 マイクロメートル以上
UNDER-PLATING:NICKEL 1.0MICROMETER MINIMUM


- テールのバラツキ寸法
TAIL COPLANARITY
240極以下品のテール平坦度は0.1MAX.、
240極品のテール平坦度は0.12MAX.とする。
TAILS COPLANARITY TO BE 0.1MAX.
IN 240 CIRCUITS, TAILS COPLANARITY TO BE 0.12MAX.
- エンボス対応済みの極数については、SD-52885-004を参照下さい。
FOR THE EMBOSSED PACKAGE PRODUCT,SEE SD-52885-004.

無し NO	80.47	78.87	75.565	84.07	52885-2474	240
	67.77	66.17	62.865	71.37	52885-2074	200
	55.07	53.47	50.165	58.67	52885-1674	160
	48.72	47.12	43.815	52.32	52885-1474	140
	42.37	40.77	37.465	45.97	52885-1274	120
	36.02	34.42	31.115	39.62	52885-1074	100
	32.85	31.25	27.94	36.45	-0974	90
	29.67	28.07	24.765	33.27	-0874	80
有り YES	26.5	24.9	21.59	30.1	-0774	70
	23.32	21.72	18.415	26.92	-0674	60
	20.15	18.55	15.24	23.75	-0574	50
	16.97	15.37	12.065	20.57	-0474	40
	13.8	12.2	8.89	17.4	-0374	30
ハウジング HS'G LOCK	10.62	9.02	5.715	14.22	52885-0274	20
CONNECTORS SERIES No.						52885-***72
極数 EMBOSSED PACKAGING CKT. NO.						


REVISED EC NO: J2010-2458 DRWN:TKA/HO CHKD:K.TOJO APPR:MSASAO REV C	DESCRIPTION 2010/06/04 2010/06/10 2010/06/11	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
				MM ONLY		---		METRIC			
		10 UNDER ±0.2		DRAWN BY M.NAGATA		DATE 2004/02/25		TITLE 0.635 PITCH B TO B S/T REC. HSG ASSY -LEAD FREE-			
		10 OVER 30 UNDER ±0.25		CHECKED BY K.TOJO		DATE 2004/02/25					
		30 OVER ±0.3		APPROVED BY M.SASAO		DATE 2004/02/25		MOLEX INCORPORATED			
		ANGULAR ±3 °		MATERIAL NO.		SEE CHART					
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
REV						DOCUMENT NO. SD-52885-003				SHEET NO. 1 OF 1	




キャリアテープ幅：24mm～56mm
CARRIER TAPE WIDTH : 24mm-56mm



キャリアテープ幅：72mm
CARRIER TAPE WIDTH : 72mm




キャリアテープ幅：88mm
CARRIER TAPE WIDTH : 88mm



キャリアテープ幅：104mm
CARRIER TAPE WIDTH : 104mm


注) NOTES

- 製品番号 52885-**72 の詳細寸法については SD-52885-003 を参照下さい。
IN THE PACKAGE , PART NO. 52885-**72 DETAILED DIMENSIONS , SEE SD-52885-003
- 梱包数量 : 1000個/リール
NUMBER OF CONNECTORS : 1000 PCS/REEL
- リードテープ長さ
LEAD TAPE LENGTH



- トップテープの剥離強度 (剥離方向は下図参照)
PEELING OFF FORCE OF TOP TAPE (PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
0.1~0.3N {10~130gf}

尚、本規格値は、出荷時に適用。
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT
(但し、輸送時に剥離が発生しない事。)
(PEEL OFF SHOULD NOT BE ALLOWED, DURING TRANSPORTATION)



- 材料
MATERIAL
キャリアテープ : ポリプロピレン (PP)
CARRIER TAPE : POLYPROPYLENE (PP)
トップテープ : PET, PE, PEF
TOP TAPE : PET, PE, PEF
リール : キャリアテープ幅 24mm~88mm : ポリスチレン
REEL : CARRIER TAPE WIDTH 24mm-88mm : POLYSTYRENE
キャリアテープ幅 104mm : 紙
CARRIER TAPE WIDTH 104mm : CARD BOARD

REVISED EC NO: J2013-1187 DRWN:TKA IHO CHKD:TASAKAWA APPR:MSASAO 2013/04/18 2013/04/18 2013/04/19	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION						
		10 UNDER	± ---	DRAWN BY M. NAGATA	DATE 2004/02/25	TITLE 52885-**72 TAPING PACKAGE -LEAD FREE-								
		10 OVER 30 UNDER	± ---	CHECKED BY K. TOJO	DATE 2004/02/25									
		30 OVER	± ---	APPROVED BY M. SASAO	DATE 2004/02/25	molex								
		ANGULAR ± --- °		MATERIAL NO.							DOCUMENT NO.			SHEET NO.
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE							SD-52885-004			1 OF 3
				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F



E

D

C

B

A



Z部詳細
DETAIL Z


断面 Y-Y
SECTION Y-Y

61.4	57.4	52.4	56 ^{+0.3}	26.2	39.9	52885-1074	100
					36.8	-0974	90
					33.6	-0874	80
49.4	45.4	40.4	44 ^{+0.3}	20.2	30.4	-0774	70
					27.2	-0674	60
					24.1	-0574	50
37.4	33.4	28.4	32 ^{+0.3}	14.2	20.9	-0474	40
					17.7	-0374	30
29.4	25.4	—	24 ^{+0.3}	11.5	14.5	52885-0274	20
F	E	D	C	キャリアテープ幅 CARRIER TAPE WIDTH	(B)	(A)	MATERIAL NO. 極致 CKT.NO.

CONNECTOR SERIES No.		52885-**72
SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION

REVISED EC NO.: J2013-1187 DRWN:TKA IHO CHKD:TASAKAWA APPR:MSASAO	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± ---	M. NAGATA	2004/02/25	TITLE 52885-**72 TAPING PACKAGE -LEAD FREE-				
		10 OVER 30 UNDER	± ---	CHECKED BY	DATE					
		30 OVER	± ---	K. TOJO	2004/02/25	APPROVED BY DATE M. SASAO 2004/02/25				
		ANGULAR ± --- °		MATERIAL NO.						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-52885-004		2 OF 3				
		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

9 8 7 6 5 4 3 2



104.4	100.4	104±0.3	50.2	84.4	52885-2474	240
88.4	84.4	88±0.3	42.2	71.7	52885-2074	200
72.4	68.4	72±0.3	34.2	59.0	52885-1674	160
				52.6	52885-1474	140
				46.3	52885-1274	120
E	D	C	キャリアテープ幅 CARRIER TAPE WIDTH	(B)	(A)	MATERIAL NO. 種数 CKT.No.

REVISED EC NO: J2013-1187 DRWN:TKAIHO 2013/04/19 CHKD:TASAKAWA 2013/04/19 APPR:MSASAO 2013/04/19	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± ---	DRAWN BY M.NAGATA	DATE 2004/02/25	TITLE 52885-**72 TAPING PACKAGE -LEAD FREE-				
		10 OVER 30 UNDER	± ---	CHECKED BY K.TOJO	DATE 2004/02/25					
		30 OVER	± ---	APPROVED BY M.SASAO	DATE 2004/02/25	molex				
		ANGULAR	± --- °	MATERIAL NO.						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-52885-004		3 OF 3		
	REV			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						