


REV	DOCUMENT	CHANGED BY	CHECK
A	0038847	PK 11APR08	ASD



1. TERMINALS WILL ACCEPT 6.35mm WIDE QUICK CONNECT RECEPTACLES AND COMPLY WITH EN61058-1 REQUIREMENTS.

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: MM				DRAWN		KSR		07APR08		Honeywell									
OPERATING FORCE: 120gf MAX. DIFFERENTIAL FORCE: RELEASE FORCE: 20gf MIN. FREE POSITION: OPERATING POSITION: 20.6±0.8MM. PRE-TRAVEL: 1.6MM MAX. DIFFERENTIAL TRAVEL: 0.4MM MAX. OVER-TRAVEL: 0.8MM MIN. FULL OVERTRAVEL FORCE:		CONTACT ARRANGEMENT S.P.D.T		TOLERANCES UNLESS NOTED: NO PLACE X ± ± ONE PLACE .X ± ± TWO PLACE .XX ± ± 0.40 THREE PLACE .XXX ± ± ANGLES X ± ± 2°				CHECK		RJ		07APR08						TITLE SWITCH - BASIC					
		  16(4)A 250V~ 25T125 µ 5E4  16A 1/2HP 125/250VAC								THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.				SIZE B		TYPE I						CAGE CODE	
				THIRD ANGLE PROJECTION 				INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		AutoCAD		SCALE		NTS				SHEET		1 OF 1			