



# NEW PRODUCT SPECIFICATION

## Model Name

# PT-1250

## P-Touch Professional Labelling Machine

### HARDWARE

Housing Dimensions	6.01'(W) x 5.1'(D) x 2.5'(H) (154 x 129 x 64 mm)
Housing Design	Handheld (horizontal long)
Housing Weight	400g
Housing Color	Blue and Yellow
Key Board	QWERTY
Number of Keys	39 keys
Cutter	Manual / Blade type
Power	AAA sized Alkaline Batteries x 6pcs or AC Adapter
LCD	Model-G 8 chr. x 1 line
Attachments	User Guide, 12 mm Black on Clear amd 12mm Black on Yellow Laminated Tapes, Carrying case and AC Adaptor Model-G
Tape Type	TZ Tape
Tape Size	6, 9, 12mm
Print Head	180 dpi / 64 dots
Print Speed	10 mm / sec.
Interface	No

### SOFTWARE

Built in Fonts	Helsinki
Number of CHRS & Symbols	180
Max. Print Height	9 mm
Max. Character Height	6.8mm
CHR Size (Pts)	11, 11p extended, 22p condensed, 22p, 22extended, Auto
CHR Widths	Extended / Medium / Condensed (Set by size setting)
Label Length Setting	No
Multi - Line	2 lines
Text Buffer	55 chrs
Memory	300 chrs (9 area)
Grace CHRs	Normal / Bold / Outline /Shadow Italic / Italic Bold / Italic Outline / Italic Shadow
Framing & Fill Pattern	Round, Banner, Wooden(Nameplate), Vine
Barcode	No
Copy Printing	1 ~ 9
Delete	Yes
Underline / Strikeout	Underline
Tape Margin Settings	None / Smalll / Half / Full
Horizontal Alignment	No
Vertical Alignment	No
Mirror Printing	Yes
Text Insert	Yes
Vertical Printing	Yes
Numbering	1 ~ 9
Split Printing	No
Battery Weak Display	Yes
Unit Change(cm / inch)	Yes
Auto Power Off	Yes