



11MM DIMENSIONS IN METRIC DO NOT SCALE DRAWING

EDP NO. SEE SHEET 2 OF 2
ENG. NO. SD-5558****
SHEET 1 OF 2




NOTES


1. APPLICABLE HOUSING : 5559 SERIES
2. MATES WITH TERMINAL : 5556 SERIES
3. (METRIC) VALUES SHOWN GOVERN OVER ENGLISH CONVERSION VALUES.
4. GENERAL TOLERANCES OF ENGLISH CONVERSION VALUES : ±.008 INCH
5. THE NUMBER OF SERRATIONS TO BE ONE FOR WIRE RANGE #22-28.



SECTION G-G



SECTION H-H



材料 MATERIAL		SEE SHEET 2 OF 2		molex MOLEX-JAPAN CO.,LTD. 日本モレックス株式会社	
K	REVISED (JC90012)	Y.K. S.K.	'98/1/6	仕上げ FINISH	SEE SHEET 2 OF 2
J	REVISED (JC80619)	Y.K. S.K.	'98/5/6	適用電線範囲 WIRE RANGE	SEE SHEET 2 OF 2
H	REVISED (J20428)	H.H. Y.Y.	'92/5/20	被覆外径 INS. RANGE	SEE SHEET 2 OF 2
G	REVISED (J10381)	H.H. Y.Y.	'91/6/25	DATE	'98/7/7
F	REVISED & REDRAWN (J10202)	H.H. Y.Y.	'91/4/27	CHK'D BY	K.T. S.KUNISHI
記号 LTR 変更内容 REVISION RECORD		DR. CHK.	DATE	APP'D BY	'98/7/7 尺度 SCALE 10 - 1
一般公差 GENERAL TOLERANCES		REVISE ONLY ON CAD SYSTEM			

角度 ANGLE	±3°	
30°以上 OVER	±0.3	
10°以上 30°未満 UNDER	±0.25	
10°未満 UNDER	±0.2	

EDP. NO.	SEE SHEET 2 OF 2
ENG. NO.	SHEET 1 OF 2
REV	K
TITLE 名称	NEW MINI. FIT CONN. CRIMP PIN

ENG. NO
SD-5558*****

EDP NO.
SEE CHART

MM DIMENSIONS IN METRIC DO NOT SCALE DRAWING

SHEET 2 OF 2

TIN PLATED PHOSPHOR BRONZE	(0.9) .035	(4.5) .177	(3.6) .142	(0.6) .024	(2.7) .106	(2.3) .091	Ø (3.1) .122 MAX.	# 16	39-00-0084	5558 PBT3L	LOOSE
									↑ -0083	↑ PBT3	CHAIN
	(0.6) .024	(2.3) .091	(2.3) .091	(0.4) .016	(1.65) .065	(1.8) .071	Ø (0.9-1.8) .035-.071	#22-28	-0068	PBT2L	LOOSE
									-0067	PBT2	CHAIN
TIN OVER COPPER PLATED BRASS	(0.9) .035	(4.5) .177	(3.6) .142	(0.5) .020	(2.3) .091	(1.9) .075	Ø (1.3-3.1) .051-.122	# 18-24	-0062	PBTL	LOOSE
									-0061	PBT	CHAIN
	(0.9) .035	(4.5) .177	(3.6) .142	(0.6) .024	(2.7) .106	(2.3) .091	Ø (3.1) .122 MAX.	# 16	-0082	T3L	LOOSE
									-0081	T3	CHAIN
	(0.6) .024	(2.3) .091	(2.3) .091	(0.4) .016	(1.65) .065	(1.8) .071	Ø (0.9-1.8) .035-.071	#22-28	-0049	T2L	LOOSE
									-0048	T2	CHAIN
	(0.9) .035	(4.5) .177	(3.6) .142	(0.5) .020	(2.3) .091	(1.9) .075	Ø (1.3-3.1) .051-.122	# 18-24	↓ -0041	↓ TL	LOOSE
									39-00-0040	5558 T	CHAIN
MATERIAL	F	E	D	C	B	A	INS. RANGE	WIRE RANGE	EDP NO.	ENG. NO.	FORM

								材料 MATERIAL	SEE CHART	molex MOLEX-JAPAN CO.,LTD. 日本モレックス株式会社
								THICKNESS : (0.203)/.008		
								仕上げ FINISH	SEE CHART	EDP. NO.
								適用電線範囲 WIRE RANGE	SEE CHART	SEE CHART
								被覆外径 INS. RANGE	SEE CHART	ENG. NO.
								DRAWN BY 9/3/02 H.HIRAMOTO	CHK'D BY 98/7/7 K.T. S.KUNISHI	SHEET 2 OF 2
								APP'D BY 98/7/7 M.FUKUSHIMA	尺度 SCALE 10 - 1	REV
								TITLE 名称 NEW MINI. FIT CONN. CRIMP PIN		

角度	ANGLE	±3°
30 以上 OVER		±0.3
10 以上 30 未満 OVER UNDER		±0.25
10 未満 UNDER		±0.2
一般公差 GENERAL TOLERANCES		

記号	変更内容	日付
LTR	REVISION RECORD	CHK. DATE

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX(JAPAN) AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
本図面は日本モレックス（株）の所有する情報を含むもので 当社の許可なく複製を禁止する。

MXJ-8