


Spherical roller bearings, cylindrical and tapered bore



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
90	160	40	325	375	39	3800	5300	3,40	22218 E *



Calculation factors

- e 0,24
- Y_1 2,8
- Y_2 4,2
- Y_0 2,8