



**Part Number: 7701NH**

LonWorks Cable Paired Cable 300 V, +80 °C

## Product Description

22 AWG, BC Conductors, Foamed Polyethylene Insulation, White LSZH Jacket, Unshielded, 1 Pair

## Technical Specifications

### Use

Suitable Applications:	Instrumentation and computer cable; For data transmission applications
------------------------	--

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
22	Solid	Bare copper	0.64 mm	1

Total Number of Conductors:	2
Total Number of Pairs:	1

#### Insulation

Material	Nominal Diameter	Diameter +/- Tolerance	Min. Wall Thickness
Polyethylene	1.17 mm	0.05 mm	0.23 mm

#### Color Chart

Number	Color
Pair 1	White/Blue & Blue/White

Color Chart1, Table Note:	Ring marking applied
---------------------------	----------------------

#### Outer Shield Material

Material
Unshielded

#### Outer Jacket Material

Material	Color	Nominal Diameter	Diameter +/- Tolerance	Min. Wall Thickness
FRNC / LSZH	White (like RAL 9003)	3.5 mm	0.4 mm	0.45 mm

### Electrical Characteristics

#### Capacitance

Nom. Capacitance Conductor to Conductor
46 pF/m

### Construction and Dimensions

#### Conductor DCR

Nominal Conductor DCR
55 Ohm/km

#### Impedance

Frequency [MHz]	Nominal Characteristic Impedance
1 - 20	100 Ohm

### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
0.772 MHz	1.3 dB/100m
1 MHz	1.5 dB/100m
4 MHz	3.1 dB/100m
10 MHz	4.9 dB/100m
16 MHz	6.3 dB/100m
20 MHz	6.9 dB/100m

### Current

Element	Max. Recommended Current [A]
Conductor	2.5 A

### Voltage

Voltage Rating [V]
300 V

### Applicable Standards & Environmental Programs

CPR Euroclass:	Dca-s2,d1,a1
Other Specification:	BS 7655 section 6.1 table 1, LTS 3

### Flame Test

ISO/IEC Flammability:	IEC 60332-3-24
-----------------------	----------------

### Safety

Amt of Halogen IEC 60754-1 /EN50267-1:	Zero
--	------

### Mechanical Characteristics

Operating Temp Range:	-15°C To +80°C
Bulk Cable Weight:	15.9(kg/km)
Max Recommended Pulling Tension:	50(N)
Min Bend Radius During Installation:	80 mm

### History

Revision Number:	3
------------------	---

### Variants

Item #	Color
7701NH.00500	WHITE
7701NH.01305	WHITE

© 2017 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.