





Visual Signals **XENON BEACONS**



- ### Features
- Continuously rated
 - High light output
 - Suitable for surface or wall mounting
 - Optional lens guard
 - 4 x M20 cable entry options
 - 360° light output around the vertical axis
 - 180° light output above the horizontal axis
 - Dustproof and Weatherproof

Material

UV Stable, Flame Retardent Polycarbonate

Industrial Xenon Beacons > X450 Series

Product overview

The X450 series is suitable for Industrial & Marine signalling applications where a visual signal is required to operate in very harsh environmental conditions.

The beacons are of the flashing mode type (single stage alarm). Xenon beacons (sometimes called strobes) are controlled via a PCB and put out a very brief but bright flash of white light by ionizing and the discharging a large current through the xenon gas in the tube.

The beacon has multiple flash rate settings, that can be set at installation, that range from 60 flashes per minute up to 180 flashes per minute to create a more noticeable warning signal to the human eye.

The units also have the ability to be fitted with a telephone initiation function and can be used as the second ring output indicator for telephones when installed in very noisy environments. Design allows for termination in the base.

X450 Series > Ordering Information

Code No:	Voltage:	Light Source:	Current:
X450-18	12-48v Dc---	Xenon 10J	0.85/0.49/0.25 A
X450-22	100-240v Ac~	Xenon 10J	0.06 A •

• at 230v Ac~

ADD THE FOLLOWING LENS CODES TO THE PRODUCT WHEN ORDERING **01** **02** **03** **04** **05**

Kg 0.5
50/60 Hz
°C -40+70
IP 66
FPM 60x180
MARINE

APPROVALS and CONFORMITIES