


Housing cover - DC-B 6-CT-M - 1602025

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

DUPLICON, aluminum housing cover, type B6, IP67 protection, with two M3 screws, V2A, captive, gasket and hole for retaining cord, for self-tapping M3 screw



Key commercial data

Packing unit	10 pc
GTIN	 4 046356 027724
Weight per Piece (excluding packing)	65.55 g
Custom tariff number	85389099
Country of origin	Slovenia

Technical data

Dimensions

Height	18 mm
Width	67 mm
Length	67 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
	IP66
	IP67
Ambient temperature (operation)	-40 °C ... 125 °C

General

Type	DC-B6
Housing type	Housing cover
Color	pearl gray
Locking type	Screw locking
Protective cover	Yes
Housing material	Aluminum die-cast
Housing surface material	EMC-conductive

Housing cover - DC-B 6-CT-M - 1602025

Technical data

General

Seal material	NBR
---------------	-----

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

VDE Gutachten mit Fertigungsüberwachung


Ex Approvals

Approvals submitted

Approval details

Housing cover - DC-B 6-CT-M - 1602025

Approvals

VDE Gutachten mit Fertigungsüberwachung 	
Nominal current IN	25 A
Nominal voltage UN	690 V

Accessories

Accessories

Device marking


Label - EML (26,5X12)R SR - 0816854



Label, Roll, silver/matt, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Adhesive, Lettering field: 26.5 x 12 mm

Drawings

Dimensioned drawing



Dimensional drawing