

Solid Tantalum Chip Capacitors

TANTAMOUNT®, Molded-Case, Built-In-Fuse Miniature



FEATURES

- Terminations: 100 % Matte Tin standard, Tin/Lead available
- Molded package available in three case codes
- Compatible with "High Volume" automatic pick and place
- Electrically activated internal fuse
- Meets EIA 535BAAC and IEC specification QC300801/US0001
- Fuse activation at 25 °C: 0.1 s max. with 5 A min. applied current
- 100 % surge current tested (D and E Case codes)



RoHS*
COMPLIANT

PERFORMANCE/ELECTRICAL CHARACTERISTICS

Operating Temperature: - 55 °C to + 125 °C

Capacitance Range: 0.47 µF to 470 µF

Voltage Rating: 4 VDC to 50 VDC

Capacitance Tolerance: ± 10 %, ± 20 %

Note: References

Molded Guide:

www.vishay.com/docs/40074/molded.pdf

Performance Characteristics:

www.vishay.com/docs/40088/perfchar.pdf

ORDERING INFORMATION

893D	106	X0	010	B	2WE3
TYPE	CAPACITANCE	CAPACITANCE TOLERANCE	DC VOLTAGE RATING AT + 85 °C	CASE CODE	TERMINATION AND PACKAGING
	This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow	X9 = ± 10 % X0 = ± 20 %	This is expressed in V. To complete the three-digit block, zeros precede the voltage rating. A decimal point is indicated by an "R" (6R3 = 6.3 V)	See Ratings and Case Codes Table	2TE3: Matte Tin, 7" (178 mm) reel 2WE3: Matte Tin, 13" (330 mm) reel 8T: Tin/Lead, 7" (178 mm) reel 8W: Tin/Lead, 13" (330 mm) reel


Notes

We reserve the right to supply higher voltage ratings and tighter capacitance tolerance capacitors in the same case size.

Voltage substitutions will be marked with the higher voltage rating.

Effective July 15, 2008, part numbers with solderable termination codes "2T" and "2W" may have either matte tin or tin/lead terminations. Codes 2TE3 and 2WE3 specify only matte tin terminations. Codes 8T and 8W specify only tin/lead terminations.



DIMENSIONS in inches [millimeters]

							
	EIA SIZE	L	W	H	P	T _W	T _H (MIN.)
C	6032 - 28	0.236 ± 0.012 [6.0 ± 0.30]	0.126 ± 0.012 [3.2 ± 0.30]	0.098 ± 0.012 [2.5 ± 0.30]	0.051 ± 0.012 [1.3 ± 0.30]	0.087 ± 0.004 [2.2 ± 0.10]	0.039 [1.0]
D	7343 - 31	0.287 ± 0.012 [7.3 ± 0.30]	0.170 ± 0.012 [4.3 ± 0.30]	0.110 ± 0.012 [2.8 ± 0.30]	0.051 ± 0.012 [1.3 ± 0.30]	0.095 ± 0.004 [2.4 ± 0.10]	0.039 [1.0]
E	7343 - 43	0.287 ± 0.012 [7.3 ± 0.30]	0.170 ± 0.012 [4.3 ± 0.30]	0.158 ± 0.012 [4.0 ± 0.30]	0.051 ± 0.012 [1.3 ± 0.30]	0.095 ± 0.004 [2.4 ± 0.10]	0.039 [1.0]


* Pb containing terminations are not RoHS compliant

RATINGS AND CASE CODES

μF	4 V	6.3 V	10 V	16 V	20 V	25 V	35 V	50 V
0.47								C
0.68								C
1.0								C
1.5							C	C
2.2						D	C	C/D
3.3						C	C	C/D
4.7					C	C	C/D	D
6.8				C	C	C	D	D/E
10			C	C	C	C/D	D	
15		C	C	C	C/D	D	D/E	
22		C	C	C/D	D	D/E	E	
33		C	C/D	C/D	D/E	E		
47		C/D	C/D	D/E	E			
68	C	C/D	D/E	D	E			
100	C	D/E	D	E				
150	D	D	D/E	E				
220	D	D/E	E					
330	D/E	E						
470	E							

CONSTRUCTION AND MARKING


Marking: Capacitors shall be marked with an anode polarity band, capacitance (in microfarads) and the rated DC working voltage 85 °C. The capacitance voltage will be separated by the letter "F" indicating a fused capacitor. Units rated at 6.3 V shall be marked as 6 V.

FUSE ACTIVATION


RATINGS AND PART NUMBER REFERENCE						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DC LEAKAGE AT + 25 °C (μ A)	MAX. DF AT + 25 °C 120 Hz (%)	MAX. ESR AT + 25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I_{rms} (A)
4 VDC AT + 85 °C, 2.7 VDC AT + 125 °C						
68	C	893D686(1)004C(2)	2.7	6	1.4	0.28
100	C	893D107(1)004C(2)	4.0	8	0.8	0.37
150	D	893D157(1)004D(2)	6.0	8	0.6	0.50
220	D	893D227(1)004D(2)	8.8	8	0.6	0.50
330	D	893D337(1)004D(2)	13.2	15	0.6	0.50
330	E	893D337(1)004E(2)	13.2	8	0.5	0.57
470	E	893D477(1)004E(2)	18.8	16	0.5	0.57
6.3 VDC AT + 85 °C, 4 VDC AT + 125 °C						
15	C	893D156(1)6R3C(2)	0.9	6	1.8	0.25
22	C	893D226(1)6R3C(2)	1.1	6	1.8	0.25
33	C	893D336(1)6R3C(2)	1.6	6	1.4	0.28
47	C	893D476(1)6R3C(2)	2.3	6	1.3	0.29
47	D	893D476(1)6R3D(2)	2.3	6	0.9	0.41
68	C	893D686(1)6R3C(2)	3.3	6	0.8	0.37
68	D	893D686(1)6R3D(2)	3.3	6	0.7	0.46
100	D	893D107(1)6R3D(2)	4.8	8	0.7	0.46
100	E	893D107(1)6R3E(2)	6.0	8	0.7	0.49
150	D	893D157(1)6R3D(2)	9.0	8	0.6	0.50
220	D	893D227(1)6R3D(2)	13.2	8	0.6	0.50
220	E	893D227(1)6R3E(2)	13.2	8	0.5	0.57
330	E	893D337(1)6R3E(2)	19.8	8	0.5	0.57
10 VDC AT + 85 °C, 7 VDC AT + 125 °C						
10	C	893D106(1)010C(2)	1.0	6	1.8	0.25
15	C	893D156(1)010C(2)	1.5	6	1.8	0.25
22	C	893D226(1)010C(2)	2.2	6	1.4	0.28
33	C	893D336(1)010C(2)	3.3	6	1.3	0.29
33	D	893D336(1)010D(2)	3.3	6	0.9	0.41
47	C	893D476(1)010C(2)	4.7	6	1.0	0.33
47	D	893D476(1)010D(2)	4.7	6	0.7	0.46
68	D	893D686(1)010D(2)	6.8	6	0.7	0.46
68	E	893D686(1)010E(2)	6.8	6	0.7	0.49
100	D	893D107(1)010D(2)	10	8	0.6	0.50
150	D	893D157(1)010D(2)	15.0	8	0.6	0.50
150	E	893D157(1)010D(2)	15.0	8	0.5	0.57
220	E	893D227(1)010E(2)	22	8	0.5	0.57
16 VDC AT + 85 °C, 10 VDC AT + 125 °C						
6.8	C	893D685(1)016C(2)	1.1	6	2.0	0.23
10	C	893D106(1)016C(2)	1.6	6	1.8	0.25
15	C	893D156(1)016C(2)	2.4	6	1.4	0.28
22	C	893D226(1)016C(2)	3.5	6	1.3	0.29
22	D	893D226(1)016D(2)	3.5	6	0.9	0.41
33	C	893D336(1)016C(2)	5.3	6	1.0	0.33
33	D	893D336(1)016D(2)	5.3	6	0.7	0.46
47	D	893D476(1)016D(2)	7.5	6	0.7	0.46
47	E	893D476(1)016E(2)	7.5	6	0.7	0.49
68	D	893D686(1)016D(2)	10.9	6	0.6	0.50
100	E	893D107(1)016E(2)	16	8	0.6	0.52
150	E	893D157(1)016E(2)	24	10	0.4	0.64

Notes

- (1) Tolerance: X0, X9
- (2) Terminations and packaging: 2TE3, 2WE3, 8T, 8W

Solid Tantalum Chip Capacitors
TANTAMOUNT®, Molded-Case, Built-In-Fuse Miniature

Vishay Sprague

RATINGS AND PART NUMBER REFERENCE						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DC LEAKAGE AT + 25 °C (μ A)	MAX. DF AT + 25 °C 120 Hz (%)	MAX. ESR AT + 25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I_{rms} (A)
20 VDC AT + 85 °C, 13 VDC AT + 125 °C						
4.7	C	893D475(1)020C(2)	0.9	6	2.0	0.22
6.8	C	893D685(1)020C(2)	1.4	6	1.9	0.24
10	C	893D106(1)020C(2)	2.0	6	1.6	0.26
15	C	893D156(1)020C(2)	3.0	6	1.4	0.28
15	D	893D156(1)020D(2)	3.0	6	0.9	0.41
22	D	893D226(1)020D(2)	4.4	6	0.7	0.46
33	D	893D336(1)020D(2)	6.6	6	0.7	0.46
33	E	893D336(1)020E(2)	6.6	6	0.7	0.49
47	E	893D476(1)020E(2)	9.4	6	0.6	0.52
68	E	893D686(1)020E(2)	13.6	6	0.6	0.52
25 VDC AT + 85 °C, 17 VDC AT + 125 °C						
2.2	C	893D225(1)025C(2)	0.9	6	2.8	0.21
3.3	C	893D335(1)025C(2)	0.8	6	2.3	0.22
4.7	C	893D475(1)025C(2)	1.2	6	1.9	0.24
6.8	C	893D685(1)025C(2)	1.7	6	1.6	0.26
10	C	893D106(1)025C(2)	2.5	6	1.4	0.28
10	D	893D106(1)025D(2)	2.5	6	1.0	0.39
15	D	893D156(1)025D(2)	3.8	6	0.8	0.43
22	D	893D226(1)025D(2)	5.5	6	0.7	0.46
22	E	893D226(1)025E(2)	5.5	6	0.7	0.49
33	E	893D336(1)025E(2)	8.3	6	0.6	0.52
35 VDC AT + 85 °C, 23 VDC AT + 125 °C						
1.5	C	893D155(1)035C(2)	0.5	6	3.8	0.17
2.2	C	893D225(1)035C(2)	0.8	6	2.9	0.20
3.3	C	893D335(1)035C(2)	1.2	4	2.0	0.23
4.7	C	893D475(1)035C(2)	1.6	6	1.8	0.25
4.7	D	893D475(1)035D(2)	1.6	6	1.2	0.35
6.8	D	893D685(1)035D(2)	2.4	6	1.0	0.39
10	D	893D106(1)035D(2)	3.5	6	0.8	0.43
15	D	893D156(1)035D(2)	5.3	6	0.7	0.46
15	E	893D156(1)035E(2)	5.3	6	0.7	0.49
22	E	893D226(1)035E(2)	7.7	6	0.6	0.52
50 VDC AT + 85 °C, 33 VDC AT + 125 °C						
0.47	C	893D474(1)050C(2)	0.5	4	6.7	0.13
0.68	C	893D684(1)050C(2)	0.5	4	5.9	0.14
1.0	C	893D105(1)050C(2)	0.5	4	4.4	0.16
1.5	C	893D155(1)050C(2)	0.8	6	3.2	0.19
2.2	C	893D225(1)050C(2)	1.1	6	2.8	0.20
2.2	D	893D225(1)050D(2)	1.1	6	2.1	0.27
3.3	C	893D335(1)050C(2)	1.7	6	2.4	0.21
3.3	D	893D335(1)050D(2)	1.7	6	1.6	0.31
4.7	D	893D475(1)050D(2)	2.4	6	1.1	0.37
6.8	D	893D685(1)050D(2)	3.4	6	0.9	0.41
6.8	E	893D685(1)050E(2)	3.4	6	0.9	0.43

Notes

- (1) Tolerance: X0, X9
- (2) Terminations and packaging: 2TE3, 2WE3, 8T, 8W



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.