

Specifications for BMP41/BMP51/BMP53 Labelmaker PermaSleeve Wiremarker Sleeves

Article No.	143232
Brady Material No.	B-342
Material Type	Heat-shrink Polyolefin Sleeve
Colour	Black on Yellow
Finish	Matt
Order Reference	MC-250-342-YL
Printer Compatibility	BMP41; BMP51; BMP53
Size - Height (mm)	11.15
Size - Length (m)	2.13
Total Qty per Pack	1 Sleeve(s) / Box
Wire Gauge	16-8
Approval/Compliance	SAE-AMS-DTL-23053/5 C (Class 1); SAE-AS-81531; MIL-STD-202 method 215K; UL224
Application	Wire & Cable Marking
Industry	Data & Telecommunications; Electrical
Layout	Continuous Roll
Description	PermaSleeve markers provide a wire marking solution that combines speed, ease of use, and permanence to create long-lasting, high quality identification. These Sleeves are self-extinguishing and meet the requirements of SAE AMS-DTL-23053/5 Class 1, SAE-AS-8153, MIL-STD-202 method 215K and is UL224 recognised
Max. Service Temp. °C	130
Max. Wire/Cable Diameter (mm)	5.46
Min. Service Temp. °C	-70
Min. Wire/Cable Diameter (mm)	2.39
Printable Sides	Single-sided Printable
Shape	Continuous
Shrink Ratio	3:1

Software

LabelMark