


NPN Silicon Planar High Voltage Transistor

TO-92

Pin Definition:

1. Emitter
2. Collector
3. Base

SOT-223

Pin Definition:

1. Base
2. Collector
3. Emitter

PRODUCT SUMMARY

BV_{CBO}	600V
BV_{CEO}	400V
I_C	1A
V_{CE(SAT)}	0.5V @ I _C / I _B = 500mA / 100mA

Features

- High BV_{ceo}, BV_{cbo}
- High current gain

Structure

- Epitaxial Planar Type

Ordering Information

Part No.	Package	Packing
TSC873CT B0	TO-92	1Kpcs / Bulk
TSC873CT A3	TO-92	2Kpcs / Ammo
TSC873CW RPG	SOT-223	2.5Kpcs / 13" Reel

Note: "G" denote for Halogen Free Product

Absolute Maximum Rating (T_a = 25°C unless otherwise noted)

Parameter	Symbol	Limit	Unit
Collector-Base Voltage	V _{CBO}	600	V
Collector-Emitter Voltage	V _{CEO}	400	V
Emitter-Base Voltage	V _{EBO}	9	V
Collector Current	DC	1	A
	Pulse	2	
Total Power Dissipation @ T _A =25°C	TO-92	1	W
	SOT-223	1.2	
Operating Junction Temperature	T _J	+150	°C
Operating Junction and Storage Temperature Range	T _{STG}	- 55 to +150	°C

Electrical Specifications (T_a = 25°C unless otherwise noted)

Parameter	Conditions	Symbol	Min	Typ	Max	Unit
Collector-Base Breakdown Voltage	I _C = 100uA	BV _{CBO}	600	--	--	V
Collector-Emitter Breakdown Voltage	I _C = 1mA	BV _{CEO}	400	--	--	V
Emitter-Base Breakdown Voltage	I _E = 100uA	BV _{EBO}	9	--	--	V
Collector-Base Cutoff Current	V _{CB} =600V	I _{CBO}	--	--	100	uA
Collector-Emitter Cutoff Current	V _{CE} = 400V	I _{CEO}	--	--	1	mA
Emitter-Base Cutoff Current	V _{EB} =8V	I _{EBO}	--	--	100	uA
Collector-Emitter Saturation Voltage	I _C = 500mA, I _B = 100mA	V _{CE(SAT)} 1	--	--	0.5	V
Collector-Emitter Saturation Voltage	I _C = 1A, I _B = 250mA	V _{CE(SAT)} 2	--	--	1	V
Base-Emitter Saturation Voltage	I _C = 500mA, I _B = 100mA	V _{BE(SAT)} 1	--	--	1	V
Base-Emitter Saturation Voltage	I _C = 1A, I _B = 250mA	V _{BE(SAT)} 2	--	--	1.2	V
DC Current Transfer Ratio	V _{CE} = 10V, I _C = 250mA	h _{FE}	80	--	--	
Trun-on Time	V _{CC} =125V, I _C =1A, I _{B1} =I _{B2} =200mA	T _{ON}	--	1	--	uS
Storage Time		T _{STG}	--	4	--	uS
Fall Time		T _{OFF}	--	0.7	--	uS

Electrical Characteristics Curve ($T_a = 25^\circ\text{C}$, unless otherwise noted)

Figure 1. Static Characteristics




Figure 2. DC Current Gain




Figure 3. VCE(sat) v.s. IC




Figure 4. VBE(sat) vs IC




Figure 5. VBE(on) vs IC






Figure 6. Safety Operation Area




TO-92 Mechanical Drawing




TO-92 DIMENSION				
DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.30	4.70	0.169	0.185
B	4.30	4.70	0.169	0.185
C	14.30(typ)		0.563(typ)	
D	0.43	0.49	0.017	0.019
E	1.18	1.28	0.046	0.050
F	3.30	3.70	0.130	0.146
G	1.27	1.31	0.05	0.051
H	0.37	0.43	0.015	0.017

Marking Diagram




- Y** = Year Code
M = Month Code
 (A=Jan, B=Feb, C=Mar, D=Apl, E=May, F=Jun, G=Jul, H=Aug, I=Sep, J=Oct, K=Nov, L=Dec)
L = Lot Code

SOT-223 Mechanical Drawing



SOT-223 DIMENSION				
DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	6.350	6.850	0.250	0.270
B	2.900	3.100	0.114	0.122
C	3.450	3.750	0.136	0.148
D	0.595	0.635	0.023	0.025
E	4.550	4.650	0.179	0.183
F	2.250	2.350	0.088	0.093
G	0.835	1.035	0.032	0.041
H	6.700	7.300	0.263	0.287
I	0.250	0.355	0.010	0.014
J	10°	16°	10°	16°
K	1.550	1.800	0.061	0.071

Marking Diagram



Y = Year Code

M = Month Code for Halogen Free Product

(**O**=Jan, **P**=Feb, **Q**=Mar, **R**=Apr, **S**=May, **T**=Jun, **U**=Jul, **V**=Aug, **W**=Sep, **X**=Oct, **Y**=Nov, **Z**=Dec)

L = Lot Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.