



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-1 GHz
- 1.2 NOMINAL IMPEDANCE: 75 OHMS
- 1.3 VOLTAGE RATING: 500 VOLTS MAX.

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
- 2.4 CRIMP FERRULE: BRASS PER JIS-C3604

3.0 FINISHES AND OTHERS

3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

- 4.1 FOR USE WITH RG179U OR SIMILAR STYLE CABLE
- 4.2 CABLE ATTACHMENT: OUTER: CRIMP, INNER: SOLDER
- 4.3 CRIMP SIZE REQUIRED: FERRULE: 3.5(.138) HEX. CRIMP TOOL
5.5(.216) HEX. CRIMP TOOL

5.0 ENVIRONMENTAL

5.1 OPERATING TEMPERATURE RANGE: -65° C TO +165° C

14	SHELL	BRASS	1	SILVER 70 μ" MIN.
13	INSULATION	TEFLON	1	NONE
12	GASKET	SILICONE	1	RED
11	WASHER	BRASS	1	NICKEL
10	SPRING WASHER	SK-5	1	NICKEL
9	WASHER	BRASS	1	SILVER 70 μ" MIN.
8	BODY II	BRASS	1	SILVER 70 μ" MIN.
7	CENTER CONTACT II	BRASS	1	SILVER 70 μ" MIN.
6	BODY I	BRASS	1	SILVER 70 μ" MIN.
5	INSULATION	TEFLON	1	NONE
4	CHASSIS	BRASS	1	SILVER 70 μ" MIN.
3	CRIMP FERRULE	BRASS	1	SILVER 70 μ" MIN.
2	INSULATION	TEFLON	1	NONE
1	CENTER CONTACT I	BRASS	1	SILVER 70 μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH



APPROVED by _____ DATE: _____

DESCRIPTION		BNC RIGHT ANGLE PLUG CRIMP								
製圖	DRAWN	TOLERANCE	品名	13-14-3	T.S.S	179U	日期	DATE	版次	REV.
	Yoko			\ROHS COMPLIANT <750>						
檢圖	CHECK	TOLERANCE	品名	DWG.NO. 13-0092						
	Arc			UNIT	mm(in)					
認定	APPROVAL	TOLERANCE	品名	SCALE						
	Jenny			ANGLE	±5°	3:1				