



## Main

Range of product	TeSys D
Product or component type	Mechanical latch block
Product compatibility	3 poles LC1D115 DC 3 poles LC1D80...D150 AC 3 poles LC1D80 DC 4 poles LC1D115 AC 4 poles LC1D115 DC 4 poles LC1D80 AC 4 poles LP1D80 DC
Control circuit voltage	220/240 V AC 50/60 Hz 220/240 V DC

## Complementary

Mounting location	Front side
Tripping control	Electrical Manual
[Ui] rated insulation voltage	690 V IEC 60947-5-1 control circuit
Power required in VA	25 AC
Power required in W	30 W DC
Mechanical durability	500000 cycles
Operating rate	1200 cyc/h
On-load factor	10 %
Product weight	0,09 kg

## Environment

Product certifications	CSA UL
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C
RoHS EUR conformity date	0629
RoHS EUR status	Compliant