

ILTS series

Submersible Dual Level & Temperature Transmitter



- **Stainless steel, piezo-resistive sensor**
- **Level accuracy: <0.1% FS BFSL**
- **Pressure ranges from 1mWG to 10mWG**
- **Temperature range: -20 to +60°C**
- **Dual independent 4-20mA outputs**

Suitable applications

River level & temperature	Reservoir level & temperature
Tank level & temperature	Borehole level & temperature
Aquifer level & temperature	Environmental monitoring
V-notch weir flow measurement	

Pressure Ranges

Nominal Pressure, Gauge	mWG	1	5	10
Permissible Overpressure	mWG	20	50	50

Temperature Range

Temperature range	°C	-20 to +60
-------------------	----	------------

Level Performance

Accuracy (Non-Linearity & Hysteresis)	<±0.1% / FS (BFSL)
Setting Errors (offsets)	Zero & Full Scale, <±0.5% / FS
Permissible Load	$R_{max} = [(Voltage\ Supply - 9) / 0.02] Ohms$
Influence Effects	Supply <0.005% FS / 1V
	Load 0.05% FS / kOhm

Temperature Performance

Measurement Accuracy	(mA output/2000) or 5µA (whichever is the greater)
Thermal drift	1 µA/°C
Loop Voltage effect	0.2µA/V
Maximum output load	$[(V_{supply} - 10) / 21] kOhms$ (Example: 700 Ohms @ 24V)
Output Timing	Transmitter start up time: 4 seconds (I out <4mA during start up) Warm up time: 1 minute to full accuracy Update time: 500ms Response time: 1 second

Output Signals and Supply Voltages

	Output	Supply Voltage	Connection	Wire Colours
Level (2-wire)	4-20mA	9-32Vdc	+ve Supply	Red
			-ve Supply	Blue
			Ground	Green
			& Cable Screen	
Temperature (2-wire) 4-20mA		9-32Vdc	+ve Supply	White
			-ve Supply	Yellow
			Ground	Green
			& Cable Screen	

The ILTS is designed for use in continuous submersion in liquids such as water, oil and fuels. The probe uses the latest piezo-resistive media-isolated silicon sensing technology and a stainless steel diaphragm. Housed within a 316L stainless steel, or high grade Duplex stainless steel housing, this submersible transmitter is the ideal product for hydrostatic level measurement where temperature is also a critical part of the measurement.

It offers excellent stability, repeatability and resolution, as required for use in rivers and reservoirs.

This type incorporates a Class 'B' accuracy platinum resistance thermometer.

Every device is temperature compensated, calibrated and supplied with a traceable serial number and calibration certificate.

Custom versions can be made for particular applications.

Cynergy3 Components Ltd.
7 Cobham Road
Ferndown Industrial Estate
Wimborne, Dorset BH21 7PE
Telephone +44 (0) 1202 897969

Email: sales@cynergy3.com
Web: www.cynergy3.com

ISO9001 CERTIFIED

ILTS 2015 RS

© 2015 Cynergy3 Components, All Rights Reserved. Specifications are subject to change without prior notice. Cynergy3 Components and the Cynergy3 Components logo are trademarks of Cynergy3 Components Limited.

www.cynergy3.com



ILTS series

Submersible Dual Level & Temperature Transmitter

Electrical Protection

Supply reverse polarity	No damage but also no function
Lightning protection	Internally fitted
Electromagnetic compatibility	CE Compliant

Mechanical Stability

Shock	100g / 11ms
Vibration	10g RMS (20 - 2000Hz)

Temperatures & Thermal Effects

Media Temperature	-20°C (Non-freezing) to +60°C
Storage temperature	-20°C to +70°C
Compensated temperature range(level only)	20°C±25°C
Thermal Zero Shift (TZS) (level only)	<±0.02% /FS/°C
Thermal Span Shift(TSS) (level only)	<-0.015% /°C
Thermal Drift (temperature only)	1µA/°C

Material Specifications

Housing	316L Stainless Steel
"O" ring seals	Viton
Diaphragm	316L Stainless Steel
Cable sheath material	PUR
Media wetted parts	Housing, "O" ring seal, diaphragm, cable sheath

Miscellaneous

Current Consumption	Level transmitter limits at 28mA Temperature transmitter limits at 21.5mA
Weight	Transmitter: approx 300g inc. nose cone Cable: 48g per meter
Installation position	Any, small zero shift when tilted through 90°
Operational Life	> 100x 10 ⁶ cycles

RS Stock No.	Part No	Pressure Range	Cable Length
8697712	ILTS-G0100-003	0-1mWG (0-39"WG)	3M
8697716	ILTS-G0500-007	0-5mWG (0-197"WG)	7M
8697725	ILTS-G1000-015	0-10mWG (0-394"WG)	15M

Mechanical Dimensions

