


GM200-24I-10-16

Thermoelectric Generator Module






Parameters for hot side temp 200°C and cold side temp 30°C

Matched load output power	4.93W
Matched load resistance	12.24Ω ± 15%
Open circuit voltage	15.54V
Matched load output	0.64A
Matched load output voltage	7.77V
Heat flow through module	~98.6W
Maximum compress (non-destructive)	1MPa
Maximum operation temperature	Hot side - 200°C. Cold side - 175°C

Features


- Compact structure (no moving parts)
- Reliable performance
- Maintenance-free
- Noise-free operation
- Low-carbon, green technology





Note: Th = hot side temperature





Note: Th = hot side temperature

