


SPECIFICATION CONTROL DRAWING



MATERIAL:

- CENTER CONTACT. GOLD PLATED BRASS (MALE) OR GOLD BERYLLIUM COPPER (FEMALE).
- HEAT SHRINKABLE INSULATION SLEEVE, TRANSPARENT BLUE. RADIATION CROSS-LINKED MODIFIED POLYVINYLDENE FLUORIDE.
- SOLDER PREFORM. Sn63 Pb37 SOLDER ALLOY WITH MILDLY ACTIVATED ROSIN FLUX.
- THREADED TRANSITION PART. SILVER PLATED BRASS.
- INSULATOR. PTFE.
- SOLDERSHIELD DEVICE. TIN PLATED COPPER BRAID WITH MILDLY ACTIVATED ROSIN FLUX.
- SOLDER PREFORM (ON L AND M SIZE ONLY). Sn63 Pb37 SOLDER ALLOY WITH MILDLY ACTIVATED ROSIN FLUX.
- HEAT SHRINKABLE INSULATION SLEEVE, BLACK. RADIATION CROSS-LINKED MODIFIED POLYOLEFIN WITH ADHESIVE.
- INSULATOR (EXCEPT FOR ANGLE PLUG), PTFE.
- BODY, NICKEL PLATED BRASS.

APPLICATION:




- THESE CONTROLLED SOLDERING DEVICES ARE DESIGNED TO CONNECT, WITH A MIL-C-390128 BNC INTERMEDIATE PART, A 50 Ω SINGLE OR DOUBLE BRAIDED COAXIAL HAVING A:
-TIN OR SILVER PLATED COPPER OUTER CONDUCTOR.
-TIN OR SILVER PLATED INNER CONDUCTOR.
AND INSULATION RATED FOR AT LEAST +85°C.
- TEMPERATURE RANGE:
* WITH BLACK SLEEVE: -55°C TO +100°C.
* WITHOUT BLACK SLEEVE: -55°C TO +150°C.
- FOR INSTALLATION PROCEDURE AND APPLICATION EQUIPMENT, CONSULT EITHER RPIP-683-00 OR RPIP-683-00-D.

FOR BEST RESULTS, PREPARE THE CABLE AS SHOWN:

PANEL THICKNESS: 3.2 MAX

For RBD-50-Y-02

For RBD-50-Y-04



If this document is printed it becomes uncontrolled.
Check for the latest revision.

tyco
Electronics

Raychem
PRODUCTS

Tyco Electronics Corporation
305 Constitution Drive
Menlo Park, CA 94025

TITLE:

ONE STEP RF CONNECTOR
50 Ω BNC

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS.

TOLERANCES:

0.00
0.0
0

ANGLES:

ROUGHNESS
IN MICRON

TYCO ELECTRONICS RESERVES THE RIGHT TO
AMEND THIS DRAWING AT ANY TIME. USERS
SHOULD EVALUATE THE SUITABILITY OF THE
PRODUCT FOR THEIR APPLICATION.

DOCUMENT NO:

RBD-50-Y-XX

CAD FILE:
D990185

REPLACES:
D981165

DRAWN:
M. FORONDA

SIZE:
A

PROD. REV.:
A

SCALE:

DOC. REV.:
3

DATE:
03-22-99

SHEET:
1 OF 1