






- 1 HOUSING MATERIAL SHALL BE LIQUID CRYSTAL POLYMER. (BLACK)
- 2 CONTACT MATERIAL SHALL BE PHOS. BRONZE. PLATING SHALL BE .000200 [0.00508] MIN. TIN/LEAD OVER .000050 [0.00127] MIN. NICKEL ALL OVER.
- 3 BASE MATERIAL SHALL BE LIQUID CRYSTAL POLYMER. (BLACK)
- 4 CONTACT MATERIAL SHALL BE PHOS. BRONZE. PLATING SHALL BE .000200 [0.00508] MIN. TIN (LEAD FREE) OVER .000050 [0.00127] MIN. NICKEL ALL OVER.

822115-4	4	6.43 [.253]	25.35 [.998]	38.20 [1.504]	2-822114-4	160
822115-3	4	7.73 [.304]	22.76 [.896]	38.20 [1.504]	2-822114-3	144
822115-4	2	6.43 [.253]	25.35 [.998]	38.20 [1.504]	822114-4	160
822115-3	2	7.73 [.304]	22.76 [.896]	38.20 [1.504]	822114-3	144
MATING COVER PART NO.	FINISH	C	B	A	PART NO.	POSN.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± .1mm [.004]
4 PLC	± -
ANGLES	± -

MATERIAL

FINISH

SEE TABLE

DWN
C.WHITT

CHK
R.MILLER

APVD
G.HOWEL

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

—

8-8-91

8-8-91

8-15-91

NAME

MICRO-PITCH SOCKET, METRIC HOUSING SUB-ASSEMBLY FOR 28mm SQUARE, .65 PITCH PQFP

SIZE

A1

DATE CODE

00779

DRAWING NO

822114

RESTRICTED TO

—

CUSTOMER DRAWING

SCALE

10:1

SHEET


1

OF


2

REV


E1



RECOMMENDED P.C. BOARD HOLE PATTERN
SOCKET SIDE
144 POSN.



RECOMMENDED P.C. BOARD HOLE PATTERN
SOCKET SIDE
160 POSN.




144 POSITION

PIN #1 IDENTIFIER

160 POSITION

PIN #1 IDENTIFIER



THIS AREA TO BE FREE OF
COMPONENTS FOR ACCESS OF
THE MICRO-PITCH HAND
TOOL. MINIMUM OF TWO
OPPOSITE SIDES.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. WHITT 8-9-91	TE Connectivity	
DIMENSIONS: INCHES		CHK R. MILLER 8-9-91		
	0 PLC	± -	APPRO G. HOWEL 8-15-91	NAME
	1 PLC	± -		
	2 PLC	± -		
	3 PLC	± -		
	4 PLC	± -	APPLICATION SPEC	SIZE
	ANGLES	± -		
MATERIAL	-	-	WEIGHT	-
CUSTOMER DRAWING		SCALE 10:1	SHEET 2 OF 2	REV E1