

# MANU-ROLL

## BLUE MANULASTIC WHEEL



### STRONG POINTS

- Very flexible materials handling
- Low starting effort.
- Non-marking tyre.



### APPLICATIONS

*Flexible and easy materials handling on all types of industrial surface, even those in poor condition.*

*Does not leave scratches or other marks on surfaces, high degree of resistance to abrasion.*

**CASTOR ASSEMBLY:** • Swivel or fixed. • Pressed steel. • Fastening by top plate. • Swivels on two rows of balls. • Bright zinc-plated protection.

**WHEEL:** • blue Manulastic: super-elastic blue rubber tyre bonded onto the black polyamide-6 centre. • Roller bearing. • Blue polycarbonate threadguards. • Bolted axle.

**LOCKING:** • **MB** Meta-bloc: double-action rear brake: wheel and swivel. • Steel pedal.

									Type		Code	EAN 13	
<b>125</b>	42	165	62	52	135x110	105x80	11	<b>250</b>			1,720	135 7222	339680 615050 4
											2,075	1 351 7222	339680 615051 1
											1,305	518 7222	339680 615052 8
<b>160</b>	42	196	62	45	135x110	105x80	11	<b>250</b>			1,980	135 7223	339680 615060 3
											2,350	1 351 7223	339680 615061 0
											1,525	518 7223	339680 615062 7
<b>200</b>	42	236	62	50	135x110	105x80	11	<b>250</b>			2,390	135 7224	339680 615070 2
											2,750	1 351 7224	339680 615071 9
											2,175	518 7224	339680 615072 6

**250**  
daN