






① HOUSING MATERIAL: LIQUID CRYSTAL POLYMER.

② CONTACT MATERIAL: PHOSPHOR-BRONZE.

③ CONTACT FINISH:(D)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
FLASH GOLD PER ASTM B 488, OVER
0.00076 MIN PALLADIUM-NICKEL OVER UNDERPLATE, OR
0.00076 MIN GOLD PER ASTM B 488 OVER UNDERPLATE.
ON LEADS:
0.00381 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.



10	5	6	1	11.88	△3	8	5536613-1					
E	D	C	B	A	FINISH	NO OF POSN	PART NUMBER					
THIS DRAWING IS A CONTROLLED DOCUMENT.					DWN D.R.BENDER 09/17/92	 TE Connectivity Z-PACK 2mm FB, POWER MODULE, RCPT. ASSY. 4 ROW, 3.53 mm LEAD LENGTH						
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:			CHK S.HEADER 01/25/93							
mm					APVD —							
		0 PLC ± — 1 PLC ± — 2 PLC ± 0.13 3 PLC ± — 4 PLC ± — ANGLES ± —			NAME							
MATERIAL		FINISH			WEIGHT	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
 					A1		00779	C=5536613		—		
CUSTOMER DRAWING					SCALE		4:1		SHEET	1 of 1	REV	A3