


Datasheet

Art.No. 58.504.9255.0

Earth terminal WT 4 E PE

Multi-tier ground DIN rail terminal block with screw connection for mounting on TS 35; nominal cross section 4 mm²; width 6 mm; color green/yellow



| | |
|------------|---------------|
| Art.No. | 58.504.9255.0 |
| EAN | 4049088164477 |
| Order unit | 100 pieces |

Approvals



Technical data

General

| | |
|--|-------------------------|
| Nominal cross section | 4 mm ² |
| Colour | Green/yellow |
| Number of levels | 2 |
| Number of clamp positions per level | 2 |
| Width/grid dimension | 6 mm |
| Insulating housing | PA666 |
| Inflammability class of insulation material acc. with UL94 | V0 |
| Mounting method | DIN rail (top hat rail) |
| Terminal blocks for electrical installations | No |

Technical data

| | |
|-----------------------------|---------------|
| Rated voltage | 800 V |
| Rated impulse voltage | 8 kV |
| Pollution degree | 3 |
| Closing plate required | Yes |
| Type of insulation material | Thermoplastic |
| Length | 59 mm |

Connection Data

| | |
|-----------------------------|----------------------|
| Connection type 1 | Screw connection |
| Connection type 2 | Screw connection |
| Minimum cross section solid | 0.14 mm ² |
| Maximum cross section solid | 6 mm ² |

| | |
|---|----------------------|
| Minimum cross section fine stranded | 0.14 mm ² |
| Maximum cross section fine stranded | 6 mm ² |
| Maximum conductor cross section (flex., stranded) with cable end sleeve | 0.5 mm ² |
| Maximum conductor cross section (flex., stranded) with cable end sleeve | 4 mm ² |
| Wire strip length | 9 mm |
| Torque conductor mounting | 0.5 Nm |

Technical Data UL/CSA

| | |
|-------------------|-----------|
| Cross section UL | 26-10 AWG |
| Voltage UL | 300 V |
| Cross section CSA | 26-10 AWG |
| Voltage CSA | 300 V |

