

Mini-Lynx GLS

ML GLS 827 E27 11W SLV

0035501

Range features



CE

PRODUCT OVERVIEW

Ordering number	0035501
Technology	Compact Fluorescent
Light colour	827 Homelight
Energy class	A
Average life (Rated) (h)	10000
Lamp shape	GLS
Lamp finish	Frosted
Dimmable	No
Cap/Base	E27
Type	GLS
EAN code	5410288355016
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	630
Efficacy (Rated) (lm/w)	57
Watt (Nominal) (W)	11
Equivalent watt (W)	50
Voltage (V)	220-240

Mini-Lynx GLS

ML GLS 827 E27 11W SLV

0035501

DATA TABLE

General data

Dry applications use only	Yes
Technology	Compact Fluorescent
Ordering number	0035501
Energy saving lamp	Yes
Average life (Rated) (h)	10000
Energy class	A
Average life (Nominal) (h)	10000
Lamp finish	Frosted
Lamp shape	GLS
Dimmable	No
Cap/Base	E27
Type	GLS
EAN code	5410288355016
E-number FI	4940414
E-number SE	8357581

Long description

Product name	ML GLS 827 E27 11W SLV
Lamp mercury content (mg)	<2
Starting time (max) (s)	<1.0
Warm-up time to 60% of full light (max) (s)	<100
Control gear required	NO
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	30000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

Optical data

Light colour	827 Homelight
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	630
Lumen maintenance at end of nominal life (%)	60
Luminous flux (Nominal) (lm)	630

Mini-Lynx GLS

ML GLS 827 E27 11W SLV

0035501

Electrical data

kWh per 1000 hours burning time	11
Efficacy (Rated) (lm/w)	57
Watt (Rated) (W)	11
Watt (Nominal) (W)	11
Equivalent watt (W)	50
Voltage (V)	220-240
Lamp power factor	=0.55

Physical data


Weight (kg)	0.07
Lamp Length (mm) - C/L	123±2
Max. Lamp Diameter (mm) - D	60±1
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	13.50 x 6.20 x 6.20
Outer package dimensions (L x W x H) (cm)	33.50 x 14.00 x 17.00

Mini-Lynx GLS

ML GLS 827 E27 11W SLV

0035501

TECHNICAL DRAWINGS



ENERGY LABEL

