

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		




LOC	DIST	REVISIONS					
AD	39	P	LTR	DESCRIPTION	DATE	DWN	APVD
			U1	ECO-06-15268	24JAN07	MB	DR

SUPERSEDED BY 3-87499-4			5	-	45.85 [1.805]	20.32 [1.800]	22.86 [1.900]	18	8-87499-9
SUPERSEDED BY 3-87499-2			5	-	43.31 [1.705]	20.32 [1.800]	20.32 [1.800]	17	8-87499-8
SUPERSEDED BY 3-87499-0			5	-	40.77 [1.605]	17.78 [1.700]	20.32 [1.800]	16	8-87499-7
SUPERSEDED BY 2-87499-8			5	-	38.23 [1.505]	17.78 [1.700]	17.78 [1.700]	15	8-87499-6
SUPERSEDED BY 2-87499-6			5	-	35.69 [1.405]	15.24 [1.600]	17.78 [1.700]	14	8-87499-5
SUPERSEDED BY 2-87499-4			5	-	33.15 [1.305]	15.24 [1.600]	15.24 [1.600]	13	8-87499-4
SUPERSEDED BY 2-87499-2			5	-	30.61 [1.205]	12.70 [1.500]	15.24 [1.600]	12	8-87499-3
SUPERSEDED BY 2-87499-0			5	-	28.07 [1.105]	12.70 [1.500]	12.70 [1.500]	11	8-87499-2
SUPERSEDED BY 1-87499-8			5	-	25.53 [1.005]	10.16 [1.400]	12.70 [1.500]	10	8-87499-1
SUPERSEDED BY 1-87499-6			5	-	22.99 [1.905]	10.16 [1.400]	10.16 [1.400]	9	8-87499-0
SUPERSEDED BY 1-87499-4			5	-	20.45 [1.805]	7.62 [1.300]	10.16 [1.400]	8	7-87499-9
SUPERSEDED BY 87499-2			5	-	17.91 [1.705]	7.62 [1.300]	7.62 [1.300]	7	7-87499-8
SUPERSEDED BY 1-87499-2			5	-	15.37 [1.605]	5.08 [1.200]	7.62 [1.300]	6	7-87499-7
SUPERSEDED BY 1-87499-0			5	-	12.83 [1.505]	5.08 [1.200]	5.08 [1.200]	5	7-87499-6
SUPERSEDED BY 87499-8			5	-	10.29 [1.405]	2.54 [1.100]	5.08 [1.200]	4	7-87499-5
SUPERSEDED BY 87499-6			5	-	7.75 [1.305]	2.54 [1.100]	2.54 [1.100]	3	7-87499-4
SUPERSEDED BY 87499-4			5	-	5.21 [1.205]	-	2.54 [1.100]	2	7-87499-3
			-	-	2.67 [1.105]	-	-	1	7-87499-2
SUPERSEDED BY 7-87499-2			-	ALL	2.67 [1.105]	-	-	1	7-87499-1
			-	-	91.57 [3.605]	43.18 [1.700]	45.72 [1.800]	36	7-87499-0
OBSOLETE			-	ALL	91.57 [3.605]	43.18 [1.700]	45.72 [1.800]	36	6-87499-9
			-	-	89.03 [3.505]	43.18 [1.700]	43.18 [1.700]	35	6-87499-8
OBSOLETE			-	ALL	89.03 [3.505]	43.18 [1.700]	43.18 [1.700]	35	6-87499-7
			-	-	86.49 [3.405]	40.64 [1.600]	43.18 [1.700]	34	6-87499-6
OBSOLETE			-	ALL	86.49 [3.405]	40.64 [1.600]	43.18 [1.700]	34	6-87499-5
			-	-	83.95 [3.305]	40.64 [1.600]	40.64 [1.600]	33	6-87499-4
OBSOLETE			-	ALL	83.95 [3.305]	40.64 [1.600]	40.64 [1.600]	33	6-87499-3
			-	-	81.41 [3.205]	38.10 [1.500]	40.64 [1.600]	32	6-87499-2
OBSOLETE			-	ALL	81.41 [3.205]	38.10 [1.500]	40.64 [1.600]	32	6-87499-1
			-	-	78.87 [3.105]	38.10 [1.500]	38.10 [1.500]	31	6-87499-0
OBSOLETE			-	ALL	78.87 [3.105]	38.10 [1.500]	38.10 [1.500]	31	5-87499-9
			-	-	76.33 [3.005]	35.56 [1.400]	38.10 [1.500]	30	5-87499-8
OBSOLETE			-	ALL	76.33 [3.005]	35.56 [1.400]	38.10 [1.500]	30	5-87499-7
			-	-	73.79 [2.905]	35.56 [1.400]	35.56 [1.400]	29	5-87499-6
OBSOLETE			-	ALL	73.79 [2.905]	35.56 [1.400]	35.56 [1.400]	29	5-87499-5
			-	-	71.25 [2.805]	33.02 [1.300]	35.56 [1.400]	28	5-87499-4
OBSOLETE			-	ALL	71.25 [2.805]	33.02 [1.300]	35.56 [1.400]	28	5-87499-3
			-	-	68.71 [2.705]	33.02 [1.300]	33.02 [1.300]	27	5-87499-2
OBSOLETE			-	ALL	68.71 [2.705]	33.02 [1.300]	33.02 [1.300]	27	5-87499-1
			-	-	66.17 [2.605]	30.48 [1.200]	33.02 [1.300]	26	5-87499-0
OBSOLETE			-	ALL	66.17 [2.605]	30.48 [1.200]	33.02 [1.300]	26	4-87499-9
			-	-	63.63 [2.505]	30.48 [1.200]	30.48 [1.200]	25	4-87499-8
			NOTES	MARKING	C	B	A	NO. OF POSN	PART NUMBER

	OBSOLETE	ALL	63.63 [2.505]	30.48 [1.200]	30.48 [1.200]	25	4-87499-7
		-	61.09 [2.405]	27.94 [1.100]	30.48 [1.200]	24	4-87499-6
	OBSOLETE	ALL	61.09 [2.405]	27.94 [1.100]	30.48 [1.200]	24	4-87499-5
		-	58.55 [2.305]	27.94 [1.100]	27.94 [1.100]	23	4-87499-4
	OBSOLETE	ALL	58.55 [2.305]	27.94 [1.100]	27.94 [1.100]	23	4-87499-3
		-	56.01 [2.205]	25.40 [1.000]	27.94 [1.100]	22	4-87499-2
SUPERSEDED BY 4-87499-2		ALL	56.01 [2.205]	25.40 [1.000]	27.94 [1.100]	22	4-87499-1
		-	53.47 [2.105]	25.40 [1.000]	25.40 [1.000]	21	4-87499-0
	OBSOLETE	ALL	53.47 [2.105]	25.40 [1.000]	25.40 [1.000]	21	3-87499-9
		-	50.93 [2.005]	22.86 [1.900]	25.40 [1.000]	20	3-87499-8
		ALL	50.93 [2.005]	22.86 [1.900]	25.40 [1.000]	20	3-87499-7
		-	48.39 [1.905]	22.86 [1.900]	22.86 [1.900]	19	3-87499-6
	OBSOLETE	ALL	48.39 [1.905]	22.86 [1.900]	22.86 [1.900]	19	3-87499-5
		-	45.85 [1.805]	20.32 [1.800]	22.86 [1.900]	18	3-87499-4
SUPERSEDED BY 3-87499-4		ALL	45.85 [1.805]	20.32 [1.800]	22.86 [1.900]	18	3-87499-3
		-	43.31 [1.705]	20.32 [1.800]	20.32 [1.800]	17	3-87499-2
	OBSOLETE	ALL	43.31 [1.705]	20.32 [1.800]	20.32 [1.800]	17	3-87499-1
		-	40.77 [1.605]	17.78 [1.700]	20.32 [1.800]	16	3-87499-0
		ALL	40.77 [1.605]	17.78 [1.700]	20.32 [1.800]	16	2-87499-9
		-	38.23 [1.505]	17.78 [1.700]	17.78 [1.700]	15	2-87499-8
		ALL	38.23 [1.505]	17.78 [1.700]	17.78 [1.700]	15	2-87499-7
		-	35.69 [1.405]	15.24 [1.600]	17.78 [1.700]	14	2-87499-6
		ALL	35.69 [1.405]	15.24 [1.600]	17.78 [1.700]	14	2-87499-5
		-	33.15 [1.305]	15.24 [1.600]	15.24 [1.600]	13	2-87499-4
		ALL	33.15 [1.305]	15.24 [1.600]	15.24 [1.600]	13	2-87499-3
		-	30.61 [1.205]	12.70 [1.500]	15.24 [1.600]	12	2-87499-2
		ALL	30.61 [1.205]	12.70 [1.500]	15.24 [1.600]	12	2-87499-1
		-	28.07 [1.105]	12.70 [1.500]	12.70 [1.500]	11	2-87499-0
		ALL	28.07 [1.105]	12.70 [1.500]	12.70 [1.500]	11	1-87499-9
		-	25.53 [1.005]	10.16 [1.400]	12.70 [1.500]	10	1-87499-8
		ALL	25.53 [1.005]	10.16 [1.400]	12.70 [1.500]	10	1-87499-7
		-	22.99 [1.905]	10.16 [1.400]	10.16 [1.400]	9	1-87499-6
		ALL	22.99 [1.905]	10.16 [1.400]	10.16 [1.400]	9	1-87499-5
		-	20.45 [1.805]	7.62 [1.300]	10.16 [1.400]	8	1-87499-4
		ALL	20.45 [1.805]	7.62 [1.300]	10.16 [1.400]	8	1-87499-3
		-	15.37 [1.605]	5.08 [1.200]	7.62 [1.300]	6	1-87499-2
		ALL	15.37 [1.605]	5.08 [1.200]	7.62 [1.300]	6	1-87499-1
		-	12.83 [1.505]	5.08 [1.200]	5.08 [1.200]	5	1-87499-0
		ALL	12.83 [1.505]	5.08 [1.200]	5.08 [1.200]	5	87499-9
		-	10.29 [1.405]	2.54 [1.100]	5.08 [1.200]	4	87499-8
		ALL	10.29 [1.405]	2.54 [1.100]	5.08 [1.200]	4	87499-7
		-	7.75 [1.305]	2.54 [1.100]	2.54 [1.100]	3	87499-6
		ALL	7.75 [1.305]	2.54 [1.100]	2.54 [1.100]	3	87499-5
		-	5.21 [1.205]	-	2.54 [1.100]	2	87499-4
		ALL	5.21 [1.205]	-	2.54 [1.100]	2	87499-3
		-	17.91 [1.705]	7.62 [1.300]	7.62 [1.300]	7	87499-2
		ALL	17.91 [1.705]	7.62 [1.300]	7.62 [1.300]	7	87499-1
		MARKING	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 21-JUN-95 E. BRANDBERG CHK 21-JUN-95 S. SHUEY APVD 21-JUN-95 D. DUPLER		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME HOUSING, MOD IV, SINGLE ROW, .100 CL, CRIMP SNAP-IN -	
MATERIAL FLAME RETARDANT		FINISH -		SIZE A2	
		WEIGHT -		CAGE CODE 00779	
				DRAWING NO G-87499	
				RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 2
				REV U1	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	39		—	SEE SHEET 1	—	—	—



- 1 PART NO & DATE CODE MARKED (WHITE), .062±.015 HIGH CHARS. IN APPROX. AREA SHOWN WHEN HOUSING SIZE PERMITS.
- 2 CAVITY IDENTS. MARKED (WHITE), .046±.015 HIGH CHARS., FIRST & EVERY FIFTH CAVITY, ONE SIDE AS SHOWN.
- 3 TOLERANCE NON-CUMULATIVE.
- 4. USE EXTRACTION TOOL 91052-1 TO REMOVE RECEPTACLE CONTACTS.
- 5 AMP LOGO MOLDED IN TEXTURED AREA AS SHOWN.
- 6 FLASH ALLOWED TO BE .015 IN THIS AREA.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. BRANDBERG 21-JUN-95	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608				
DIMENSIONS: mm		CHK S. SHUEY 21-JUN-95	NAME HOUSING, MOD IV, SINGLE ROW, .100 CL, CRIMP SNAP-IN —				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. DUPLER 21-JUN-95					
	0 PLC ± — 1 PLC ± — 2 PLC ± 0.13[.005] 3 PLC ± — 4 PLC ± — ANGLES ± —	PRODUCT SPEC — APPLICATION SPEC — WEIGHT —					
MATERIAL FLAME RETARDANT	FINISH —	CUSTOMER DRAWING		SIZE A2	CAGE CODE 00779	DRAWING NO C-87499	RESTRICTED TO —
				SCALE 4:1	SHEET 2 OF 2	REV U1	