


Contact insert module - HC-M-PN3-MOD-ST-BU - 1663475

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

HEAVYCON pneumatic module, male/female, 3 connections



Key commercial data

Packing unit	2 pc
Minimum order quantity	2 pc
GTIN	 4 017918 123284
Weight per Piece (excluding packing)	7.83 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Electrical characteristics

Note	Hinged retaining frame HC-M-MHR...is required for HEAVYCON-ADVANCE housing of types B6 to B24 and HEAVYCON housing of types B6 to B48, pneumatic HC-M-PN... male and female connectors (Pneumatic male and female connectors not included in the scope of supply)
Number of positions	3

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

Mechanical characteristics

Internal diameter of pressure hose connection	4 mm
Insertion/withdrawal cycles	≥ 500

General

Color	blue
Number of module slots	1
Inflammability class according to UL 94	V0

Contact insert module - HC-M-PN3-MOD-ST-BU - 1663475

Technical data

General

Assembly instructions	HC-CST (1676857) coding pins and HC-CBU (1676860) coding sockets are mandatory. Observe the minimum bending radii when connecting the hoses.
Connection	<ul style="list-style-type: none"> - Lock together the pneumatic contact with the module. To do so, insert the contact into the module from the front. - Place the modules fitted with the contacts in the hinged retaining frame. The hinged retaining frame is fixed after insertion with HC-M-MHR-FIX (opening prevented). - The pneumatic hoses are pushed onto the pneumatic contact from the rear module side. The medium-sized module slots and sleeves/coupling housing with straight cable outlet direction are recommended

Material data

Contact carrier material	PC
--------------------------	----

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000438
ETIM 3.0	EC000438
ETIM 4.0	EC000438
ETIM 5.0	EC000438

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Approvals

Approvals

Contact insert module - HC-M-PN3-MOD-ST-BU - 1663475

Approvals

Approvals


GOST / UL Recognized

Ex Approvals

Approvals submitted


Approval details

GOST 

UL Recognized 

Drawings

Dimensioned drawing



3-pos.