

Denna ritning är Pressmaster AB:s egendom. Skyddad av gällande lag.
This drawing is the property of Pressmaster AB. Protected in accordance with privailing law.

För icke direkt toleranssatta mått
gäller toleransklass



General tolerances if not other-
wise stated

NOM DIM MM		TOL CLASS		
From	To	A	B	C
(1)	6	±0.05	±0.1	±0.2
(6)	30	±0.1	±0.2	±0.5
(30)	100	±0.15	±0.3	±0.8
(100)	300	±0.2	±0.5	±1.2
(300)	1000	±0.3	±0.8	±2

Hål / Holes H13


Skarpa kanter brutna där ej annat anges.
No sharp edges unless otherwise specified.

Övriga generella toleranser enligt
ritning 4100-4644.
Additional general tolerances in
accordance with drawing 4100-4644.



4101-0274

4300-3767



FÖRSPÄNNING / PRELOAD: 130 ± 20 N

Tolkmått / Gauge dimensions (mm)		
URTAG	Gåtolk	Stopptolk
NEST	GO	NO GO
6.65	ø6.60	ø6.70
8.23	ø8.18	ø8.28
9.70	ø9.65	ø9.75

Material			Behandling/Treatment				Status	
							Frisläppt	
Konstr/Design	Ritad/Drawn	Datum/Date		Skala/Scale	Kontr/Checked	Godk/Approved	Ämne/Blank	
OS	TGW	2009-11-03		1:2	IP	NE		
pressmaster® ISO 9001 REG NR FM13687 			Benämning/Denomination KRIMPTÅNG 298-1074 CRIMPING TOOL			Vikt/Veight, gram		Art grp 012
						Ritn nr/Drawing no		REV
						43002438		008