



M 6/8 - 0 to 10 mm² (22 to 8 AWG), 50 Amps, 8 mm

M 6/8

M 6/8.P...

Spacing 8 mm (.315")

Spacing 8 mm (.315")



Terminal block for ground wire

Standard 8 mm block

[View correct mounting of ground block on rail](#)

		Type	P/N	
Standard blocks	Grey body	M 6/8	115 118.11	
	Blue body	M 6/8.N	125 118.13	
	Yellow body	M 6/8	105 118.20	
	Orange body	M 6/8	105 004.22	
	Green body	--	--	
	Red body	--	--	
	Black body	--	--	
Terminal blocks for ground wires	Green / yellow body (with rail contact)	M 6/8.P	165 114.17	
	Yellow+green body (without rail contact)	M 6/8.PI	165 451.21	
Characteristics		DIN-VDE	UL	CSA
Wire size mm ² / AWG**	Solid wire	0 - 10	22-8	24-8
	Stranded wire	0 - 6	AWG	AWG
Rated voltage	V AC / = DC	750/900 Gr.C	600	600
Rated current	A	46	50	55
Rated wire size	mm ² / AWG	6 mm ²	8 AWG	8 AWG
Wire stripping length	mm / inches	12 mm / .47"		
Recommended torque	Nm /lb.in	0.8-1 Nm / 7.1-8.9 lb-in		

Accessories	Type	P/N
-------------	------	-----

	End stop (all rails)		BAM	th. 9.1	103 002.26
	End section	grey	FEM6	*th. 2.8	118 368.16
		blue	FEM6	*th. 2.8	128 368.10
		yellow	FEM6	th. 2.8	103 062.21
		orange	FEM6	*th. 2.8	103 126.16
		green	FEM6	*th. 2.8	103 125.15
	Circuit separator	grey	SCM6	*	113 003.10
	Separator end section (block)	grey	SCF6	*th. 3	118 707.03
	Separator end section (rail)	grey	SCFM6	th. 3	114 825.05
	Test socket	DIA. 2 mm	AL2 (1)	*	163 043.21
		DIA. 3 mm	AL3 (1)	*	163 261.00
		DIA. 4 mm	AL4 (1)	*	163 262.01
	Test device		DCO	*orange	173 060.00
	Test plug	DIA. 2 mm	FC2	*DIA. 2	007 865.26
	Preassembled jumper bar <i>IP20 touchproof</i>	2 poles	BJM8 (1)	*	168 520.05
		3 poles	BJM8 (1)	*	168 521.22
		4 poles	BJM8 (1)	*	168 522.23
		5 poles	BJM8 (1)	*	168 523.24
		10 poles	BJM8 (1)	*	168 974.00
	Connector plate		EL6	*	173 627.21
	Jumper bar not preassembled Post+screw+washer		BJS8 (1)	*20 poles	174 789.05
			EV6	*	168 604.16
	Comb-type jumper bar	10 poles	PC8	*	163 313.24
	Isolating cover				
	Shielding connector		--	--	--
	Protection label	3 blocks	EP6	*	163 427.17
	Screw for protection label	4 blocks	EP8	*	163 428.20
			VSP6	*	163 433.15
	See markers section		RC810 Side		