

Low-Voltage Single SPDT Analog Switch

DESCRIPTION

The DG9411 is a single-pole/double-throw monolithic CMOS analog switch designed for high performance switching of analog signals. Combining low power, high speed (t_{ON} : 9 ns, t_{OFF} : 5 ns), low on-resistance ($r_{DS(on)}$: 7 Ω) and small physical size (SC70), the DG9411 is ideal for portable and battery powered applications requiring high performance and efficient use of board space.

The DG9411 is built on Vishay Siliconix's low voltage J12 process. An epitaxial layer prevents latchup. Break-before-make is guaranteed for DG9411.

Each switch conducts equally well in both directions when on, and blocks up to the power supply level when off.

FEATURES

- Low voltage operation (2.25 V to 5.5 V)
- Low on-resistance - $r_{DS(on)}$: 7 Ω
- Fast switching - t_{ON} : 9 ns, t_{OFF} : 5 ns
- Low charge injection - Q_{INJ} : 5 pC
- Low power consumption
- TTL/CMOS compatible
- 6-Pin SC70 package



Available
RoHS*
COMPLIANT


BENEFITS

- Reduced power consumption
- Simple logic interface
- High accuracy
- Reduce board space

APPLICATIONS

- Cellular phones
- Communication systems
- Portable test equipment
- Battery operated systems
- Sample and hold circuits

FUNCTIONAL BLOCK DIAGRAM AND PIN CONFIGURATION



TRUTH TABLE

Logic	NC	NO
0	ON	OFF
1	OFF	ON

Logic "0" $\leq$ 0.8 V

Logic "1" $\geq$ 2.4 V

ORDERING INFORMATION

Temp Range	Package	Part Number
- 40 to 85 $^{\circ}$ C	SC70-6	DG9411DL-T1 DG9411DL-T1-E3

* Pb containing terminations are not RoHS compliant, exemptions may apply.

ABSOLUTE MAXIMUM RATINGS

Parameter	Limit	Unit
Reference V ₊ to GND	- 0.3 to + 6	V
IN, COM, NC, NO ^a	- 0.3 to (V ₊ + 0.3)	
Continuous Current (Any Terminal)	± 50	mA
Peak Current (Pulsed at 1 ms, 10 % duty cycle)	± 200	
Storage Temperature	- 65 to 150	°C
Power Dissipation (Packages) ^b	6-Pin SC70 ^c	250
		mW

Notes:

a. Signals on NC, NO, or COM or IN exceeding V₊ will be clamped by internal diodes. Limit forward diode current to maximum current ratings.

b. All leads welded or soldered to PC Board.

c. Derate 3.1 mW/°C above 70 °C.

SPECIFICATIONS V₊ = 2.5 V

Parameter	Symbol	Test Conditions Unless Otherwise Specified V ₊ = 2.5 V, ± 10 % V _{IN} = 0.4 or 2.0 V ^e	Temp ^a	Limits - 40 to 85 °C			Unit
				Min ^b	Typ ^c	Max ^b	
Analog Switch							
Analog Signal Range ^d	V _{NO} , V _{NC} V _{COM}		Full	0		V+	V
Drain-Source On-Resistance	r _{DS(on)}	V ₊ = 2.25 V, V _D = 1.0 V, I _S = 10 mA	Room Full ^d		26 29	35 40	Ω
r _{DS(on)} Flatness ^d	r _{DS(on)} Flatness	V ₊ = 2.5 V	Room		10		
Switch Off Leakage Current ^f	I _{S(off)}	V ₊ = 2.75 V, V _S = 0.5 V/1.5 V, V _D = 1.5 V/0.5 V	Room Full ^d	- 250 - 3.0		250 3.0	pA nA
	I _{D(off)}		Room Full ^d	- 250 - 3.0		250 3.0	pA nA
Channel-On Leakage Current ^f	I _{D(on)}	V ₊ = 2.75 V, V _S = V _D = 0.5 V/1.5 V	Room Full ^d	- 250 - 3.0		250 3.0	pA nA
Digital Control							
Input High Voltage	V _{INH}		Full	2			V
Input Low Voltage	V _{INL}		Full			0.4	
Input Capacitance ^d	C _{in}		Full		3		pF
Input Current	I _{INL} or I _{INH}	V _{IN} = 0 or V ₊	Full	- 1		1	μA
Dynamic Characteristics							
Turn-On Time	t _{ON}	V _D or V _S = 1.5 V, R _L = 300 Ω, C _L = 35 pF Figures 1 and 2	Room Full ^d		16	40 45	ns
Turn-Off Time	t _{OFF}		Room Full		7	23 28	
Break-Before-Make Time	t _d		Room ^d	1	12		
Charge Injection ^d	Q _{INJ}	C _L = 1 nF, V _{GEN} = 0 V, V _S = 0 V, R _{GEN} = 0 Ω, Figure 3	Room		5	10	pC
Off-Isolation ^d	OIRR	R _L = 50 Ω, C _L = 5 pF, f = 1 MHz	Room		- 73		dB
Crosstalk ^d	X _{TALK}		Room		- 70		
Source-Off Capacitance ^d	C _{S(off)}	V _{IN} = 0 or V ₊ , f = 1 MHz	Room		7		pF
Channel-On Capacitance ^d	C _{D(on)}		Room		20		
Drain-to-Source Capacitance ^d	C _{DS(off)}		Room		20		
Power Supply							
Power Supply Range	V ₊			2.25		2.75	V
Power Supply Current ^d	I ₊	V _{IN} = 0 or V ₊			0.01	1.0	μA
Power Consumption	P _C					0.3	μW









SPECIFICATIONS V+ = 3 V							
Parameter	Symbol	Test Conditions Unless Otherwise Specified V+ = 3 V, ± 10 % VIN = 0.4 or 2.0 V ^e	Temp ^a	Limits - 40 to 85 °C			Unit
				Min ^b	Typ ^c	Max ^b	
Analog Switch							
Analog Signal Range ^d	VNO, VNC VCOM		Full	0		V+	V
Drain-Source On-Resistance ^d	rDS(on)	V+ = 2.7 V, VD = 1.5 V, IS = 10 mA	Room Full		15 19	25 30	Ω
rDS(on) Flatness ^d	rDS(on) Flatness	VS = 0 to V+, IS = 10 mA	Room		7.5		
Switch Off Leakage Current ^f	IS(off)	V+ = 3.3 V, VS = 1 V/3 V, VD = 3 V/1 V	Room Full	- 500 - 4.0		500 4.0	pA nA
	ID(off)		Room Full	- 500 - 4.0		500 4.0	pA nA
Channel-On Leakage Current ^f	ID(on)	V+ = 3.3 V, VS = VD = 1 V/3 V	Room Full	- 500 - 4.0		500 4.0	pA nA
Digital Control							
Input High Voltage	VINH		Full	2			V
Input Low Voltage	VINL		Full			0.8	
Input Capacitance ^d	Cin		Full		3		pF
Input Current	IINL or IINH	VIN = 0 or V+	Full	- 1		1	μA
Dynamic Characteristics							
Turn-On Time ^d	tON	VD or VS = 2.0 V, RL = 300 Ω, CL = 35 pF Figures1 and 2	Room Full		12	15 20	ns
Turn-Off Time ^d	tOFF		Room Full		6	8 10	
Break-Before-Make Time ^d	td		Room	1	7		
Charge Injection ^d	QINJ	CL = 1 nF, VGEN = 0 V, VS = 0 V, RGEN = 0 Ω, Figure 3	Room		5	10	pC
Off-Isolation ^d	OIRR	RL = 50 Ω, CL = 5 pF, f = 1 MHz	Room		- 73		dB
Crosstalk ^d	XTALK		Room		- 70		
Source-Off Capacitance ^d	CS(off)	VIN = 0 or V+, f = 1 MHz	Room		7		pF
Channel-On Capacitance ^d	CD(on)		Room		20		
Drain-to-Source Capacitance ^d	CDS(off)		Room		20		
Power Supply							
Power Supply Range	V+			2.7		3.3	V
Power Supply Current	I+	VIN = 0 or V+			0.01	1.0	μA
Power Consumption	PC					0.4	μW

SPECIFICATIONS V+ = 5 V							
Parameter	Symbol	Test Conditions Unless Otherwise Specified V+ = 5 V, ± 10 % VIN = 0.8 or 2.4 V ^e	Temp ^a	Limits - 40 to 85 °C			Unit
				Min ^b	Typ ^c	Max ^b	
Analog Switch							
Analog Signal Range ^d	VNO, VNC VCOM		Full	0		V+	V
Drain-Source On-Resistance	rDS(on)	V+ = 4.5 V, VD = 3 V, IS = 10 mA	Room Full		7 10	12 16	Ω
rDS(on) Flatness ^d	rDS(on) Flatness	V+ = 2.5 V	Room		2		
Switch Off Leakage Current	IS(off)	V+ = 5.5 V, VS = 1 V/4.5 V, VD = 4.5 V/1 V	Room Full	- 1.0 - 4.0		1.0 4.0	nA
	ID(off)		Room Full	- 1.0 - 4.0		1.0 4.0	
Channel-On Leakage Current	ID(on)	V+ = 5.5 V, VS = VD = 1 V/4.5 V	Room Full	- 1.0 - 3.0		1.0 4.5	
Digital Control							
Input High Voltage	VINH		Full	2.4			V
Input Low Voltage	VINL		Full			0.8	
Input Capacitance	Cin		Full		3		pF
Input Current	IINL or IINH	VIN = 0 or V+	Full	- 1		1	μA
Dynamic Characteristics							
Turn-On Time ^d	tON	VD or VS = 3 V, RL = 300 Ω, CL = 35 pF Figure 1 and 2	Room Full		9	11 15	ns
Turn-Off Time ^d	tOFF		Room Full		5	7 9	
Break-Before-Make Time ^d	td		Room	1	4		
Charge Injection ^d	QINJ	CL = 1 nF, VS = 0 V, VGEN = 0 V, RGEN = 0 Ω, Figure 3	Room		5	10	pC
Off-Isolation ^d	OIRR	RL = 50 Ω, CL = 5 pF, f = 1 MHz	Room		- 73		dB
Crosstalk ^d	XTALK		Room		- 70		
Source-Off Capacitance ^d	CS(off)	VIN = 0 or V+, f = 1 MHz	Room		7		pF
Channel-On Capacitance ^d	CD(on)		Room		20		
Drain-to-Source Capacitance ^d	CDS(off)		Room		20		
Power Supply							
Power Supply Range	V+			4.5		5.5	V
Power Supply Current	I+	VIN = 0 or V+			0.01	1.0	μA
Power Consumption	PC					0.6	μW


Notes:

- Room = 25 °C, Full = as determined by the operating suffix.
- The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this datasheet.
- Typical values are for design aid only, not guaranteed nor subject to production testing.
- Guarantee by design, nor subjected to production test.
- V_{IN} = input voltage to perform proper function.
- Guaranteed by 5 V leakage testing, not production tested.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted

 $r_{DS(on)}$ vs. Analog and Power Voltage

 $r_{DS(on)}$ vs. Analog Voltage and Temperature

Supply Current vs. Temperature

Supply Current vs. Input Switching Frequency

Leakage Current vs. Temperature

Leakage vs. Analog Voltage


TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




Switching Time vs. Temperature and Supply Voltage




Crosstalk and Off Isolation vs. Frequency





Input Switching Threshold vs. Supply Voltage







Insertion Loss vs. Frequency



Charge Injection vs. Analog Voltage

TEST CIRCUITS


Logic "1" = Switch On
Logic input waveforms inverted for switches that have the opposite logic sense.

Figure 1. Switching Time

Figure 2. Break-Before-Make Interval


IN depends on switch configuration: input polarity determined by sense of switch.

Figure 3. Charge Injection

TEST CIRCUITS




Figure 4. Off-Isolation






Figure 5. Channel Off/On Capacitance



SC-70: 6-LEADS



Dim	MILLIMETERS			INCHES		
	Min	Nom	Max	Min	Nom	Max
A	0.90	—	1.10	0.035	—	0.043
A ₁	—	—	0.10	—	—	0.004
A ₂	0.80	—	1.00	0.031	—	0.039
b	0.15	—	0.30	0.006	—	0.012
c	0.10	—	0.25	0.004	—	0.010
D	1.80	2.00	2.20	0.071	0.079	0.087
E	1.80	2.10	2.40	0.071	0.083	0.094
E ₁	1.15	1.25	1.35	0.045	0.049	0.053
e	0.65BSC			0.026BSC		
e ₁	1.20	1.30	1.40	0.047	0.051	0.055
L	0.10	0.20	0.30	0.004	0.008	0.012
α	7°Nom			7°Nom		

ECN: S-03946—Rev. B, 09-Jul-01
DWG: 5550



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.