

Wiha SoftFinish®.

The specialist for dry and general applications.




1997



The right tool at a glance,
thanks to the printed screw symbol
on the handle end.

The Wiha SoftFinish® zone features a solid moulded core with soft outer grip. This requires less force, yet achieves 40% more torque than conventional handles. The handle is shaped to fit comfortably in the hand, providing maximum torque forces in dry and general working conditions.

If a stuck screw has to be loosened, a precise hammer blow can be applied to the solid steel cap. Due to the hex blade extending through the handle to the steel cap, there is no loss of impact energy.



The solid steel cap at the end of the SoftFinish® handle enables controlled hammer blows, for example, when loosening a tight screw.

Due to the solid steel cap and hex blade extending through the handle, there is no loss of impact energy when a precise hammer blow is applied.



Thermoplastic elastomer tolerates high loads and feels soft and pleasant to the touch.

Blade with hex bolster for wrenches to use on particularly tight screws.



Wiha SoftFinish®.

- Multi-component SoftFinish® handle provides maximum user comfort
- Ergonomically perfect handle design
- Printed screw symbol on handle end for fast identification
- Available in versions with round blade, hex blade or hex blade with solid steel cap
- Blade made of high quality CVM-steel, through-hardened and chrome plated
- Wiha ChromTop®-finish on tip for a perfect fit every time

For slotted screws.



302 SoftFinish® slotted cabinet screwdriver.

Round blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN 5265, DIN ISO 2380.

Application: Especially for dry and general applications.

Order-No.	⌀	→	⊖	●	→	→	→
00684 6	2.0•	65	0.4	2.0	169	23	10
00685 3	2.5	75	0.4	2.5	179	23	10
00686 0	3.0•	80	0.5	3.0	184	23	10
00687 7	3.0	100	0.5	3.0	204	23	10
00689 1	3.0•	150	0.5	3.0	254	23	10
00690 7	3.0•	200	0.5	3.0	304	23	10
32383 7	3.0	300	0.5	3.0	404	23	5
00691 4	3.5	100	0.6	3.5	204	23	10
26931 9	3.5•	200	0.5	3.5	304	23	10
00692 1	4.0	100	0.8	4.0	211	30	10
00694 5	4.0•	150	0.8	4.0	261	30	10
00695 2	4.0•	200	0.8	4.0	311	30	10
00696 9	4.0•	300	0.8	4.0	411	30	5
27753 6	4.5•	80	0.8	4.5	191	30	10
00697 6	4.5•	125	0.8	4.5	236	30	10
00698 3	5.5	125	1.0	5.5	236	30	10
00700 3	5.5	150	1.0	5.5	261	30	10
00701 0	5.5•	200	1.0	5.5	311	30	10
00702 7	5.5•	300	1.0	5.5	411	30	5
32384 4	6.0	300	1.0	6.0	418	36	5

• Additional dimension. Non-DIN size.



302 SoftFinish® slotted workshop screwdriver.

Round blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN 5265, DIN ISO 2380.

Application: Especially for dry and general applications.

Order-No.	⌀	→	⊖	●	→	→	→
27754 3	6.0	100	1.0	5.5	218	36	10
27755 0	6.0	150	1.0	5.5	268	36	10
00704 1	6.5	100	1.2	6.0	218	36	10
00703 4	6.5	150	1.2	6.0	268	36	10
00706 5	6.5•	200	1.2	6.0	318	36	5
00708 9	8.0	150	1.2	7.0	274	41	10
00707 2	8.0	175	1.2	7.0	299	41	5
00709 6	8.0	175	1.6	7.0	299	41	5
32399 8	8.0	300	1.2	7.0	424	41	5
00711 9	10.0	200	1.6	8.0	324	41	5
32400 1	10.0	300	1.6	8.0	424	41	5
00712 6	12.0	250	2.0	8.0	374	41	5
00713 3	14.0	250	2.5	11.0	374	41	5

• Additional dimension. Non-DIN size.

For slotted screws.



308 SoftFinish® slotted screwdriver.

Hex blade with hex bolster.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN 5265, DIN ISO 2380.

Application: Especially for dry and general applications.

Order-No.	⌀	→	⊖	●	⊖	→	→	
00731 7	3.5	75	0.6	4.0	-	186	30	10
00732 4	4.5•	90	0.8	4.0	-	201	30	10
00733 1	5.5	100	1.0	5.0	8	213	36	10
00734 8	6.5	125	1.2	6.0	10	238	36	10
00735 5	7.0•	125	1.1	6.0	10	238	36	10
00736 2	8.0	150	1.2	8.0	13	268	41	10
00737 9	9.0•	150	1.4	8.0	13	268	41	10
00738 6	10.0	175	1.6	8.0	13	293	41	5
00739 3	12.0	200	2.0	10.0	16	318	41	5
00740 9	14.0	250	2.5	10.0	16	368	41	5

• Additional dimension. Non-DIN size.



530 SoftFinish® slotted screwdriver.

Hex blade with hex bolster, solid steel cap.

Order-No.	⌀	→	⊖	●	⊖	→	→	
03223 4	3.5	75	0.6	4.0	-	186	30	10
03224 1	4.5•	90	0.8	4.0	-	201	30	10
03225 8	5.5	100	1.0	5.0	8	213	36	10
03226 5	6.5	125	1.2	6.0	10	238	36	10
03228 9	8.0	150	1.2	8.0	13	271	41	5
03230 2	10.0	175	1.6	8.0	13	296	41	5
03231 9	12.0	200	2.0	10.0	16	321	41	5
03232 6	14.0	250	2.5	10.0	16	371	41	5

• Additional dimension. Non-DIN size.



398 SoftFinish® slotted screw-holding screwdriver.

Clamping sleeve holds the screw.

Blade: Chrome-vanadium steel, through hardened, black-finish.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: For setting and turning screws in difficult to access areas.

Order-No.	⌀	→	⊖	→	→	→
32867 2	2.5	75	0.4	186	30	5
32868 9	3.0	100	0.5	211	30	5
32869 6	4.0	125	0.8	243	36	5
32870 2	5.0	150	1.0	268	36	5
32871 9	6.0	175	1.2	293	36	5