


Application

Precision video cables are used in critical analog and digital video circuits and high quality applications such as live broadcast in network studios and pre- or post-production facilities

Construction & Dimensions



- 1. Conductor**
- 2. Dielectric**
- 3.1 Foil**
- 3.2 Braid**
- 4. Jacket**

- 1. Inner Conductor** Innenleiter - Conduttore Interno - Conducteur - Conductor - Проводник
Material solid, bare copper
Diameter 0.64 mm
- 2. Dielectric** Dielektrikum - Dielettrico - Diélectrique - Dieléctrico - Диэлектрик
Material Gas injected Foam HDPE
Diameter over insulation 2.80 mm
- 3. Outer Conductor** Aussenleiter - Conduttore Esterno - Conducteur extérieur - Conductor externo - Внешний проводник
Material foil + braid
Diameter screen 3.4 mm

3.1 Shielding foil Duofoil®
Coverage: 100%
3.2 Shielding braid tinned copper braid
Coverage 90% ± 5%
- 4. Jacket** Aussenmantel - Guaina - Gaine - Revestimiento - Оболочка
Material FRNC/LSNH, UV-resistant, IEC 332-1
Diameter: 4.45 ± 0.2 mm
Color and text: see table Marking

Requirements and test methods

Electrical characteristics

Mean characteristic impedance: $75 \pm 3 \Omega$

Wellenwiderstand - Impedenza Caratteristica Principale - Impédance nominale - Características eléctricas - Электрические характеристики

Nominal capacitance conductor to shield: 53.0 pF/m

Kapazitaet - Capacità Nominale Conduttore/Schermo - Capacité nominale entre conducteur et blindage - Capacitancia nominal de conductor a blindaje - Номинальная емкость "проводник-экран"

Nominal velocity of propagation: 84%

Ausbreitungsgeschwindigkeit - Velocità Nominale di Propagazione - Vitesse de propagation nominale - Velocidad nominal de propagación - Номинальная скорость распространения сигнала

Max. DC loop resistance: 69.0 Ω /km
Schleifenwiderstand – Resistenza continua di Loop – Resistenza (DC) di Loop - Resistencia de bucle CC - Сопротивление петли пост. Тока

Max. inner conductor DC resistance @ 20 °C: 52.0 Ω /km
Gleichstromwiderstand Innenleiter - Resistenza Nominale DC del Conduttore Interno - Résistance du conducteur intérieur - Resistencia CC nominal del conductor interno - Номин. сопротивление пост. тока внутреннего проводника при

Max. outer conductor DC resistance @ 20 °C: 17.0 Ω /km
Gleichstromwiderstand Aussenleiter - Resistenza Nominale DC del Conduttore Esterno - Résistance du conducteur extérieur - Resistencia CC nominal del conductor externo - Номин. сопротивление пост. тока внутреннего проводника при

Return loss at 5-1600 MHz: ≥ 23 dB
1600-4500 MHz: ≥ 21 dB

Rueckflusssdaempfung - Perdite Cumulative di Riflessione - Taux de réflexion du signal - Pérdida de retorno - Обратные потери на

Screening attenuation at

30-3000 MHz: ≥ 85 dB
3000-4500 MHz: ≥ 80 dB

Schirmungsmass – Attenuazione dello Schermo- L'affaiblissement lié au blindage - Eficacia de blindaje - Эффективность экранирования

Nominal Attenuation: Wellendaempfung - Attenuazione Nominale – Affaiblissement - Atenuación nominal - Номинальное затухание

1 MHz:	1.7 dB/100m	180 MHz:	13.2 dB/100m
3.6 MHz:	2.5 dB/100m	270 MHz:	16.1 dB/100m
5 MHz:	2.8 dB/100m	360 MHz:	18.6 dB/100m
6 MHz:	3.0 dB/100m	540 MHz:	22.8 dB/100m
7 MHz:	3.2 dB/100m	720 MHz:	26.4 dB/100m
10 MHz:	3.7 dB/100m	750 MHz:	26.9 dB/100m
12 MHz:	4.0 dB/100m	1000 MHz:	31.3 dB/100m
25 MHz:	5.4 dB/100m	1500 MHz:	38.7 dB/100m
67.5 MHz:	8.3 dB/100m	2000 MHz:	45.0 dB/100m
71.5 MHz:	8.6 dB/100m	2250 MHz:	48.0 dB/100m
88.5 MHz:	9.5 dB/100m	2500 MHz:	50.8 dB/100m
100 MHz:	10 dB/100m	3000 MHz:	56.1 dB/100m
135 MHz:	11.5 dB/100m	4000 MHz:	65.7 dB/100m
143 MHz:	11.9 dB/100m	4500 MHz:	70.2 dB/100m

Mechanical and physical characteristics

Temperature range - storage/operation -15°C to +75°C

Temperature range - installation -5 °C to + 75°C

Minimum bending radius 10x Ø cable

Biegeradius - Raggio Minimo di Curvatura - Rayon de courbure minimum - Radio de curvatura mínimo - Минимальный радиус изгиба

Nominal cable weight 27.9 kg/km

Gewicht - Peso Nominale del Cavo – Poids - Peso nominal del cable - Номинальный вес кабеля

Ordering information

MARKING

Jacket colour	Text
Green	VIDEO BRILLIANCE (R) BY BELDEN 1855ENH - 0.6/2.8 DUOFOIL(R) + BRAID - FRNC SDV - LFH

Meter marking: yes, MM-YY: month and year of manufacturing

PACKAGING (PUT-UP)

100m and 500m

Each reel is labelled with the following data:

Belden Logo, Belden code number, item description, length on the reel and date of manufacturing.