



Main

Range of product	Zelio Relay
Product or component type	Plug-in relay
Device short name	RHK
Contacts type and composition	4 C/O
Contacts operation	Latching Standard
Control circuit voltage	24 V DC
[the] conventional enclosed thermal current	5 A at $\leq 40\text{ }^{\circ}\text{C}$
Status LED	Without
Control type	Manual control
Coil interference suppression	Without

Complementary

[Ui] rated insulation voltage	250 V
Operating position	Any position
Minimum switching capacity	150 mVA at 10 mA 150 mVA / 1 V
Contact bounce time	$\leq 10\text{ ms}$
Voltage drop	$\leq 100\text{ V}$ for 3 A at 24 V
Average resistance	30 mOhm at 20 °C
Switching time	1...4 ms for energisation/de-energisation 1.2...4 ms for de-energisation/energisation
Average consumption in W	1.6 W at 20 °C on coil 1 2.9 W at 20 °C on coil 2
Control circuit voltage limits	0.8...1.1 U_c conforming to IEC 60255
Drop-out voltage threshold	0.1...0.3 U_c
Time constant	12 ms for open contact(s) 15 ms for closed contact(s)
Mechanical durability	10000000 cycles
Operating rate	$\leq 2\text{ cyc/mn}$
Operating time	10...14 ms between energisation of trip coil and closing of NC contact at 20 °C 12...22 ms between energisation of coil and closing of NO contact at 20 °C
Minimum pulse duration	$\geq 50\text{ ms}$
CAD overall width	33 mm
CAD overall height	43 mm
CAD overall depth	90 mm
Terminals description ISO n°1	(11-12-14)OC (21-22-24)OC (31-32-34)OC (41-42-44)OC (A1-A2)CO (B1-B2)CO
Product weight	0.14 kg

Environment

Standards	BS 4794 IEC 255 NF C 45-250 VDE 0435
Product certifications	ASE BV CSA EDF UR USSR
Protective treatment	TC
Dielectric strength	2500 V
Ambient air temperature for operation	-5...40 °C conforming to IEC 60255
Ambient air temperature for storage	-40...70 °C
Vibration resistance	6 gn (f = 10...55 Hz) conforming to IEC 60068-2-6 6 gn (f = 10...55 Hz) conforming to NF C 20-616
Shock resistance	30 gn for 11 ms conforming to NF C 20-608