


NO	DESCRIPTION	DATE
△	BRASS → STAINLESS STEEL	05.15.95'
△	MODIFICATION FOR CENTER CONTACT	07.24.02'
△	BACKGROUND FORMAT UPDATED	02.02.09'
△	ADD 3.2	07.27.10'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-600 MHz
 1.2 NOMINAL IMPEDANCE: 50 OHM

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
 2.2 CENTER CONTACT: BRASS PER JIS-C3604
 2.3 INSULATION: TEFLON PER ASTM D6457 AND ASTM D6710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.
 3.2 RADIAL TORQUE OF CENTER CONTACT: NO APPLICABLE △

4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -55° C TO +125° C

7	BODY	BRASS	1	NICKEL 100μ" MIN.
6	INSULATION	TEFLON	1	NONE
5	CENTER CONTACT	BRASS	1	GOLD 50μ" MIN
4	INSULATION	TEFLON	1	NONE
3	WASHER	STAINLESS STEEL	1	NONE
2	GASKET	SILICONE	1	RED
1	SHELL	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH



APPROVED

by _____ DATE: _____

DESCRIPTION		FME PLUG-SMA PLUG	
製圖	DRAWN Yoko	TOLERANCE .X ±0.2	品名 23-14 T.G.N
檢圖	CHECK Jacky	.XX ±0.1	TITLE ROHS COMPLIANT (500)
認定	APPROVAL Lewis	.XXX ±0.05	DATE 04.29.93
		ANGLE ±5°	REV. A-4
			DWG.NO. 23-0046
			UNIT mm(in)
			SCALE 4:1