




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		J	REVISED PER ECO-12-012320	05JUL12	KH	MZ

D

C



B

A



- 1
- 0.76µm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH GOLD FLASH ON THE REMAINDER OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
- 2
- 1.27µm [.000050] MIN TIN-LEAD PER MIL-T-10727 OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
- 3
- 0.76µm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH A UNIFORM GRADIENT TO 0.25µm [.000010] MIN GOLD PER MIL-G-45204 ON THE REMAINDER OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
- 4
- 0.38µm [.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27µm [.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
- 5
- GOLD PLATING NOT REQUIRED IN THIS AREA.
- 6
- WIRE RANGE 18-16 AWG. INSULATION RANGE 2.03[.080]-2.54[.100].
- 7
- 0.38µm [.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN, 1.27µm [.000050] MIN TIN-LEAD PER MIL-T-10727 FOR A LENGTH OF 5.69 [.224] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL PER QQ-N-290 ON ENTIRE CONTACT.
- 8
- 1.27µm [.000050] MIN TIN PER MIL-T-10727 OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
- 9
- 0.76µm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08[.200]MIN WITH 1.27µm [.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 0.76µm [.000050] MIN NICKEL PER QQ-N-290.

	STANDARD		CU-NI ALLOY	2-66358-1	1-66360-6
	STANDARD		CU-NI ALLOY	2-66358-0	1-66360-5
	STANDARD		CU-NI ALLOY	1-66358-9	1-66360-4
	SMALL PACK		BRASS	1-66358-6	1-66360-3
	STANDARD		BRASS	1-66358-6	1-66360-2
	SMALL PACK		BRASS	66358-4	1-66360-1
	SMALL PACK		BRASS	66358-2	1-66360-0
OBSOLETE	STANDARD		BRASS	1-66358-5	66360-9
	STANDARD		PHOSPHOR BRONZE	1-66358-3	66360-8
OBSOLETE	STANDARD		PHOSPHOR BRONZE	1-66358-2	66360-7
	STANDARD		BRASS	66358-4	66360-4
	STANDARD		BRASS	66358-3	66360-3
	STANDARD		BRASS	66358-2	66360-2
	STANDARD		BRASS	66358-1	66360-1
	PACKAGING	BODY FINISH	BODY MATERIAL	STRIP P/N REF	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 06/03/92		 TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK W.LENKER 6-11-92			
		APVD G.STEINHAUER 7-8-92		NAME SOCKET ASSEMBLY, LOOSE PIECE, TYPE III+	
		PRODUCT SPEC —			
		APPLICATION SPEC —		SIZE A2	
		—			
MATERIAL		WEIGHT —		CAGE CODE 00779	
SEE CALLOUTS		FINISH		DRAWING NO C=66360	
				RESTRICTED TO —	
				SCALE 8:1	
				SHEET 1 of 1	
				REV J	