


CONNECTOR SPECIFICATION:

VOLTAGE RATING	250 VAC/VDC
AMPERAGE RATING	max. 4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-30°C TO 80°C
UL CERTIFICATIONS	UL STYLE 2464
CSA CERTIFICATIONS	I/II A/B 80°/300V

ITEM	COMPONENT	MATERIAL	FINISH
6	O-RING	VITON	RED
5	COUPLER	BRASS	NICKEL PLATED
4	PIN CONTACT	COPPER ALLOY	GOLD OVER NICKEL
3	INSERT	NYLON	BLACK
2	OVERMOLD	POLYURETHANE (PUR)	YELLOW
1	CABLE- 22/3-5 (COPPER STRANDING) 3/4/5 CONDUCT. 300V	JACKET: PVC	JACKET: BLACK



DESCRIPTION EC NO: WEU2010-0283 DRWN: LSTEMMLE 2010/01/20 CHKD: NS APPR: NSTAUDIG 2010/01/26	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>±---</td><td>±---</td></tr><tr><td>3 PLACES</td><td>±---</td><td>±---</td></tr><tr><td>2 PLACES</td><td>±---</td><td>±.01</td></tr><tr><td>1 PLACE</td><td>±0.3</td><td>±---</td></tr><tr><td colspan="3">ANGULAR ± --- °</td></tr></table>		mm	INCH	4 PLACES	±---	±---	3 PLACES	±---	±---	2 PLACES	±---	±.01	1 PLACE	±0.3	±---	ANGULAR ± --- °			DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
				mm	INCH																				
			4 PLACES	±---	±---																				
			3 PLACES	±---	±---																				
			2 PLACES	±---	±.01																				
			1 PLACE	±0.3	±---																				
			ANGULAR ± --- °																						
			DRAWN BY ----		MICRO-CHANGE CORDSET 3/4/5-POL FE STR SE 22/3-5 PVC BLACK CABLE																				
			DATE ----																						
			CHECKED BY RE		DATE 2010/01/21																				
APPROVED BY NSTAUDIG		DATE 2010/01/25																							
MATERIAL NO. SEE TABLE SHEET 2		DOCUMENT NO. SD-120065-038																							
SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SHEET NO. 1 OF 1																							
1	REV																								

POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
3	1200060001	803000E03M020	6.56' +3.50" -0 [2.0M +88.9 -0]

POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
4	1200060014	804000E03M020	6.56' +3.50" -0 [2.0M +88.9 -0]

POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
5	1200060634	805000E03M020	6.56' +3.5" -0 (2.0M +89mm -0)

DESCRIPTION EC NO: WEU2010-0283 DRWN: LSTEMMLE 2010/01/20 CHKD: NS APPR: NSTAUDIG 2010/01/26	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION		
		▽ = 0  = 0		mm	INCH	DRAWN BY		DATE		MICRO-CHANGE CORDSET 3/4/5-POL FE STR SE 22/3-5 PVC BLACK CABLE		
			4 PLACES	±---	±---	----		----				
			3 PLACES	±---	±---	CHECKED BY		DATE				
			2 PLACES	±---	±.01	RE		2010/01/21				
			1 PLACE	±0.3	±---	APPROVED BY		DATE				
			ANGULAR ± --- °			NSTAUDIG		2010/01/25		 MOLEX INCORPORATED		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		SEE TABLE					
					SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
							DOCUMENT NO.		SD-120065-038		SHEET NO. 1 OF 1	