



1/2" DR. STRAP OIL FILTER WRENCH

PART NO.	SIZE INCH			G.W. (kg)
97441	18"	4	32	6.6



- Use wrench on oil filters up to a 120mm diameter
- Strong nylon belt will not slip
- Use with 1/2" drive tools or 13/16" wrench tools

PISTON RING COMPRESSORS



PART NO.	SIZE INCH			G.W. (kg)
97501	3"	6	60	10.0
97502	4"	6	30	11.0



- Positive lock action provides positive compression and fingertip release
- Heavy spring steel compresses the stiffest rings evenly
- Tool is beaded along lower edge to prevent compressor from entering the cylinder

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.



VALVE SEAL RING PLIERS

PART NO.			G.W. (kg)
97511	6	48	10.0





- For pulling valve shafts sealing rings and removing valve spring supports

ELECTRICAL WIRE STRIPPER AND CRIMPER **New**

PART NO.			G.W. (kg)
97521	10	40	12.8





DROP FORGED COIL SPRING COMPRESSORS

PART NO.	SIZE MM			G.W. (kg)
97701	270	2	12	19.0
97702	370	2	12	23.0



- Simplify the job of removing & replacing shock absorbers and struts
- Suitable for use where space under wheel arch is limited

HYDRAULIC BOTTLE JACK



PART NO.	MAXI LOAD			G.W. (kg)
97801	2T	1	6	21.0
97802	5T	1	4	24.0
97803	3T	1	6	3.8
97804	8T	1	4	6.6
97805	10T	1	4	7.1
97806	20T	1	1	10.6
97807	30T	1	1	21.7
97808	50T	1	1	30.7



- All steel construction
- Designed for use in automotive, industrial, construction or agricultural jobs for lifting, pushing, bending and straightening
- Adjustable top screw
- Fewer working parts, extremely smooth bearing surfaces, and close tolerances ensure trouble-free service and long life. Screw adjustable pad Jacks can be used in vertical and horizontal positions

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.

ROTATING HANDLE HYDRAULIC FLOOR JACK



PART NO.	MAXI LOAD			G.W. (kg)
97811	2T	1	1	17.0
97812	3T	1	1	20.0



- Designed for use in heavy duty truck, heavy construction and agricultural equipment maintenance garages
- Chromed ram and dust seals on floor jack prevent hydraulic contamination
- Safety by-pass and overload systems protect hydraulic block
- Additional foot pedal pumping provides fast saddle raising to the load
- Spring loaded "T" handle on floor jack can be activated to lower load in any handle position by pulling and rotating it clockwise 1/4 turn
- High carbon steel chassis provides maximum strength in a lightweight floor jack design

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.

LONG RAM JACK-PORTABLE HYDRAULIC EQUIPVBAT



PART NO.	MAXI LOAD			G.W. (kg)
97821	4T	1	1	20.0




- Easy to maintain, easy to clean remote control jacks deliver power where you need it, especially in hard to reach places on automotive frames and bodies
- They include pump, ram, and connecting hose with quick coupler for fast easy detachment

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.

SCISSORS JACK

PART NO.	MAXI LOAD			G.W. (kg)
97831	1.5T	1	10	42.0



- Lifting range 95 - 350mm
- Supplied complete with cranking handle

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.