



Plastic bracket (accessory)

- Extremely high light intensity of more than 15 cd
- Life duration up to 50,000 hrs
- High impact resistance to 20 Joules
- DC multi-voltage version

### **i** TECHNICAL SPECIFICATIONS:

|                                 |  |
|---------------------------------|--|
| Dimensions (Diameter x Height): | 142 mm x 220 mm  |
| Housing:                        | PC/ABS-Blend   |
| Dome:                           | PC, transparent  |
| Fixing:                         | Base mounting, bracket mounting (accessory), tube mounting (accessory)                               |
| Connection:                     | Screwable conn. with wire protection max. 2.5 mm <sup>2</sup><br>Contact protection according to VDE |
| Cable entry:                    | Cable diameter 5-7 mm  |
| Life duration:                  | up to 50,000 hrs   |
| Duty cycle:                     | 100 %  |

**Life duration up to 50,000 hrs**

### **🛒** ORDER SPECIFICATIONS:

|                     |                   |                   |
|---------------------|-------------------|-------------------|
| Voltage             | 12-50 V =         | 230 V ~           |
| Current consumption | 12 V: 500 mA      | 50 mA             |
|                     | 50 V: 100 mA      |                   |
| red                 | <b>280 100 55</b> | <b>280 100 68</b> |
| yellow              | <b>280 300 55</b> | <b>280 300 68</b> |

### **🏠** ACCESSORIES:

|                                       |                   |
|---------------------------------------|-------------------|
| Plastic bracket for wall mounting     | <b>975 883 06</b> |
| Flange for tube mounting max. 25.3 mm | <b>975 883 02</b> |
| Wire guard                            | <b>975 883 08</b> |

### **📏** TECHNICAL DIAGRAMS:

see page 240



Extremely high light output using unique LED technology.



Plastic bracket, flange for tube mounting and wire guard (accessories)

