

General Information

Extended Product Type:	ZK6
Product ID:	1SNK708010R0000
EAN:	3472597080104
Catalog Description:	ZK6 PI-Spring clamp Terminal Block - Feed-through - Grey
Long Description:	Combine high performance with compact dimensions: - 1000 V AC / DC IEC 600 V UL, - Opt for the best marking visibility thanks to the up-front, flat marker zone, which lets you mark up to eight digits or increase the font size.

Additional Information

ABB Industrial IT Suite:	Control IT
ATEX Certificate:	1SND162009A1702
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Ambient Temperature:	-5 ... +40 °C
BV Certificate:	1SND162013A0203
CB Certificate:	1SND162016A0200
CSA Certificate:	1SND162014A0205
Color:	Grey
Connecting Capacity Main Circuit UL/CSA:	Spring Clamp / Rigid 1x 24 ... 8 AWG Spring Clamp / With Insulated Ferrule 1x 24 ... 10 AWG Spring Clamp / Without Insulated Ferrule 1x 24 ... 10 AWG
Connecting Capacity UL/CSA:	Stranded 8 AWG
Connecting Capacity Main Circuit:	Spring Clamp / Flexible 1x 0.5 ... 6 mm ² Spring Clamp / Rigid 1x 0.5 ... 10 mm ² Spring Clamp / With Insulated Ferrule 1x 0.5 ... 6 mm ² Spring Clamp / Without Insulated Ferrule 1x 0.5 ... 6 mm ² Spring Clamp / With Twin Ferrule 2x 0.5 ... 1.5 mm ²
Connection Type:	PI Spring
Country of Origin:	France (FR)
Customs Tariff Number:	85369010
DNV Certificate:	1SND162023A0200
Data Sheet, Technical Information:	1SNK162029D0201
Declaration of Conformity - CE:	1SND225112U1001
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Dielectric Test Voltage:	2200 V
EAC Certificate:	1SND161010A1100
EAN:	3472597080104
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block
Environmental Information:	1SND220072E1002
Flammability According to UL94:	V0
Function:	Feed-through
Gauge Type:	A5 & 3.9 mm Dia.
IT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNK160027C0201

Insulation Material:	Polyamide
Invoice Description:	ZK6 PI-Spring clamp Terminal Block - Feed-through - Grey
Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Minimum Order Quantity:	50 piece
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Connections:	2
Number of Levels:	1
Object Classification Code:	X
Order Multiple:	50 piece
Package Level 1 EAN:	3472597080104
Package Level 1 Gross Weight:	0.64 kg
Package Level 1 Height:	46 mm
Package Level 1 Length:	201 mm
Package Level 1 Units:	50 piece
Package Level 1 Width:	119 mm
Package Level 2 Gross Weight:	7.680 kg
Package Level 2 Height:	200 mm
Package Level 2 Length:	400 mm
Package Level 2 Units:	450 piece
Package Level 2 Width:	300 mm
Package Level 3 Units:	21600 piece
Pollution Degree:	3
Power Loss:	1.3 W
Product Main Type:	ZK6
Product Name:	Terminal Block
Product Net Depth:	41.9 mm
Product Net Height:	57.5 mm
Product Net Length:	41.9 mm
Product Net Weight:	11.8 g
Product Net Width:	8 mm
Product Packing Type:	Box
Rated Cross-Section:	6 mm ²
Rated Current (I_n):	Main Circuit 41 A
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Rated Short-time Withstand Current (I_{cw}):	for 1 s 720 A
Rated Voltage (U_r):	1000 V
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Date:	20110608
RoHS Information:	1SND230535F0201
RoHS Status:	Following EU Directive 2011/65/EC
Selling Unit of Measure:	piece
Short-Circuit Current Rating (SCCR):	100 kA
Spacing:	8 mm
Sub-Function:	2 connections
Sub-Function 3:	2 connections
Wire Stripping Length:	12.5 mm
cUL Certificate:	1SND162012A0203

Number of Potentials:

1

IECEX Certificate:

1SND162010A1702

