



ENGLISH

Datasheet

Stock No: 543- 658

RS Pro 14.5mm Hand; Hydraulic Circular Punch & Die Combinations



Product Details

Circular Hole Cutter

Circular hole cutters suitable for use on mild steel (28 tons/in² uts max) up to 1.6mm (16 swg) and aluminium up to 2mm (14 swg).

Long life punches. Minimum burr, distortion or surface damage.

Easy to dismantle - slugs drop freely out of die.

Most punches can be used with the hydraulic pump/cylinder or hydraulic hand punch kit up to 35mm/1 1/4 in diameter (see comparison table for exceptions). Not suitable for lever presses.

Specifications:

Hole Shape	Circular
Operation	Hand; Hydraulic
Hole Size	14.5mm
Cutting Capacity	Mild Steel: 1.6 mm; Aluminium: 2 mm