


## 190 Series Multi Purpose 19" Rack




*Multi purpose 19" rack manufactured in ABS in 3, 4, 5, 6, 9, and 12U heights.*

The 190 series is moulded in ABS using 5.5mm thick U forms for the top and base with either 1U or 3U side panels that snap together to change the height from the smallest 3U height to 4,5,6, 9 and 12U maximum.

Four 1.5mm coated steel vertical profiles fit inside the ABS shells providing a standard DIN41494 and IEC 297-2 19" rack platform. Good airflow is provided by using as standard a 193 cm<sup>2</sup> ventilation area which is moulded into both the top and bottom covers. The 190 comes complete with integrated feet and the assembled unit can be stacked by using these in conjunction with the corresponding moulded recesses. Two recessed carry handles in both the top and bottom mouldings allow portability, even when stacked.

- Designed to house standard 19" card cages and 19" sub racks
- Choice of front panels and internal supports
- Flexible low cost solution
- Accessories include castors, tilting feet, internal trays and 19" attachment sets



Part No.	Dimensions (mm)		
	W	H	D
3U 190-32190003	529	178.6	400
4U 190-32190004	529	223.1	400
5U 190-32190005	529	267.5	400
6U 190-32190006	529	312	400
9U 190-32190009	529	445.4	400
12U 190-32190012	529	578.8	400

All specifications are subject to change without notice.

To order, specify as following example:

Part No  
190-32190003