


## EM-DUO/120/15/GFI

Order No.: 5600462

Figure shows the variant 5600461 EM-DUO 120/15



Rail-mountable double socket with integrated fault current circuit breaker, for mounting on 35 mm DIN rails in acc. with EN 60715, housing color: White, with screw connection, national version: USA



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

### Commercial data

EAN	4046356139526
Pack	1 Pcs.
Customs tariff	85366990
Weight/Piece	0.3104 KG
Catalog page information	Page 513 (IF-2007)

### Technical data

#### General data

Nominal voltage $U_N$	120 V AC
Nominal current $I_N$	15 A
For country-specific use in	USA
Color	white
Insulating material	PVC 94 V0
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Standards/regulations	UL 508
Length	134 mm
Width	83 mm
Height	52 mm

---

### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	6 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	4 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	10
Type of connection	Screw connection
Stripping length	8 mm
Screw thread	M 3

### Certificates / Approvals

Approval logo




### requested approbations


Certification	CUL Listed, UL Listed
---------------	-----------------------

### Drawings

Connection diagram



Dimensioned drawing



Circuit diagram

