

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	39		L2	REVISED PER ECO-11-004587	11MAR11	RK	HMR

D

C

B




A

D

C

B

A



- 1
- TRUE POSITION TOLERANCE OF POST TIPS APPLIES WHEN HEADERS ARE HELD FLAT AGAINST PC BOARD.
- 2
- .000015 GOLD IN CONTACT AREA, GOLD FLASH ON SOLDER AREA, ALL OVER .000050 NICKEL.
- 3
- POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 4
- PARTS PACKAGED IN SINGLE TUBES.
- 5
- HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK
POST: PHOS.BRONZE.
- 6
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

6 4	OBSOLETE	.284	.200	2	3	4-87224-3	
	6 OBSOLETE	3.984	3.900	39	40	4-87224-0	
		3.884	3.800	38	39	3-87224-9	
		3.784	3.700	37	38	3-87224-8	
		3.684	3.600	36	37	3-87224-7	
		3.584	3.500	35	36	3-87224-6	
		3.484	3.400	34	35	3-87224-5	
		3.384	3.300	33	34	3-87224-4	
		3.284	3.200	32	33	3-87224-3	
		3.184	3.100	31	32	3-87224-2	
		3.084	3.000	30	31	3-87224-1	
		2.984	2.900	29	30	3-87224-0	
		2.884	2.800	28	29	2-87224-9	
		2.784	2.700	27	28	2-87224-8	
		2.684	2.600	26	27	2-87224-7	
		2.584	2.500	25	26	2-87224-6	
		2.484	2.400	24	25	2-87224-5	
		2.384	2.300	23	24	2-87224-4	
		2.284	2.200	22	23	2-87224-3	
		2.184	2.100	21	22	2-87224-2	
2.084	2.000	20	21	2-87224-1			
6	OBSOLETE	1.984	1.900	19	20	2-87224-0	
	6	OBSOLETE	1.884	1.800	18	19	1-87224-9
		1.784	1.700	17	18	1-87224-8	
		1.684	1.600	16	17	1-87224-7	
6	OBSOLETE	1.584	1.500	15	16	1-87224-6	
		1.484	1.400	14	15	1-87224-5	
		1.384	1.300	13	14	1-87224-4	
		1.284	1.200	12	13	1-87224-3	
		1.184	1.100	11	12	1-87224-2	
		1.084	1.000	10	11	1-87224-1	
		.984	.900	9	10	1-87224-0	
		.884	.800	8	9	87224-9	
		.784	.700	7	8	87224-8	
		.684	.600	6	7	87224-7	
		.584	.500	5	6	87224-6	
		.484	.400	4	5	87224-5	
		.384	.300	3	4	87224-4	
		.284	.200	2	3	87224-3	
		.184	.100	1	2	87224-2	
		.084	—	—	1	87224-1	
		C	B	A	NO OF POS	PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	RAGHAVENDRA		24FEB09		 TE Connectivity						
DIMENSIONS: INCHES		CHK	GESFORD JEFFREY		24FEB09								
		APVD	GESFORD JEFFREY		24FEB09		NAME HEADER ASS'Y MOD II, .025 SQ POST, SINGLE ROW, 100 C/L, STACKABLE						
		PRODUCT SPEC —											
		APPLICATION SPEC —				SIZE A2		CAGE CODE 00779		DRAWING NO C-87224		RESTRICTED TO —	
		WEIGHT —											
MATERIAL 		FINISH 		CUSTOMER DRAWING				SCALE 4:1		SHEET 1 OF 1		REV L2	