





LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			BI	REVISED PER ECO-11-004835	11MAR2011	RK	HMR



SECTION **A - A**
SCALE 20 : 1



1. WIRE RANGE .13 - .35 mm² (26 -22 AWG).
2. INSULATION RANGE 0.89 - 1.65 [.035 - .065].
3. 0.00038 [.000015] MIN GOLD STRIPE IN LOCALIZED AREA
OVER 0.00127 [.000050] MIN NICKEL OVER ENTIRE CONTACT
-OR-
GOLD FLASH OVER PALLADIUM-NICKEL .00038 [.000015] MIN
TOTAL IN LOCALIZED AREA OVER .00127 [.000050] MIN NICKEL
OVER ENTIRE CONTACT.
4. 0.00076 [.000030] MIN GOLD STRIPE IN LOCALIZED AREA
OVER 0.000127 [.000050] MIN NICKEL OVER ENTIRE CONTACT.
-OR-
GOLD FLASH OVER PALLADIUM-NICKEL .00076 [.000030] MIN
TOTAL IN LOCALIZED AREA OVER .00127 [.000050] MIN NICKEL
OVER ENTIRE CONTACT.
5. NOT FOR USE IN HOUSING PART NUMBER 770602.
6. CONTACTS COATED WITH ANTI-FRETTING LUBRICANT.



SECTION **B-B**
SCALE 20:1

	PH BRZ	1445336-3
	PH BRZ	1445336-2
PRE-TIN	PH BRZ	1445336-1
FINISH	MATERIAL	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 21-JUNE-2001 K. WHITTAKER CHK 21-JUNE-2001 J. ELLIS APVD 21-JUNE-2001 J. ELLIS		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ±- 1 PLC ±- 2 PLC ±0.13 [0.005] 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC 108-1948 APPLICATION SPEC 114-13036	
MATERIAL		FINISH		SIZE	CAGE CODE
SEE TABLE		SEE TABLE		A2	00779
				DRAWING NO	
				C-1445336	
		WEIGHT		RESTRICTED TO	
		-		-	
CUSTOMER DRAWING				SCALE	SHEET
				15.1	OF 1
				REV	B1