

# Plug - QP 1,5/ 1-L - 3051014

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plug, Connection method: Quick connection, Number of positions: 1, Cross section: 0.25 mm<sup>2</sup> - 1.5 mm<sup>2</sup>, AWG: 24 - 16, Width: 5.2 mm, Height: 40 mm, Color: gray

Illustration shows various versions of the product (left, center and right element) in different color combinations

## Product description

Connector element left, left housing without engagement pin, right opened without cover

## Why buy this product

- The conductor is connected using the familiar IDC connection with no stripping, therefore saving time
- Tested for railway applications
- The QT-COMBI plugs for self-assembly provide solutions that users can implement themselves
- The QP 1,5/... fast connector plug is designed for the connection of solid and stranded conductors



## Key commercial data

Packing unit	50 pc
GTIN	 4 046356 082464
Weight per Piece (excluding packing)	4.03 g
Custom tariff number	85366990
Country of origin	Poland

## Technical data

### General

Number of levels	1
Number of connections	1
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0
Area of application	Railway industry
	Mechanical engineering

# Plug - QP 1,5/ 1-L - 3051014

## Technical data

### General

	Plant engineering
Maximum load current	17.5 A (with 1.5 mm <sup>2</sup> conductor cross section)
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 61984
Nominal current I <sub>N</sub>	17.5 A
Nominal voltage U <sub>N</sub>	500 V
Number of positions	1

### Dimensions

Width	5.2 mm
Length	20 mm
Height	40 mm

### Connection data

Connection in acc. with standard	IEC 61984
Connection method	Quick connection
Conductor cross section solid min.	0.25 mm <sup>2</sup>
Conductor cross section solid max.	1.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max.	16
Conductor cross section stranded min.	0.25 mm <sup>2</sup>
Conductor cross section stranded max.	1.5 mm <sup>2</sup>
Min. AWG conductor cross section, stranded	24
Max. AWG conductor cross section, stranded	16
Material wire insulation	PVC / PE
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	VDE 0295 Cl.1-5
Max. wire diameter incl. insulation	3 mm

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

# Plug - QP 1,5/ 1-L - 3051014

## Classifications

### ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002021
ETIM 5.0	EC002021

### UNSPSC

UNSPSC 6.01	30211802
UNSPSC 7.0901	39121402
UNSPSC 11	39121402
UNSPSC 12.01	39121402
UNSPSC 13.2	39121402

## Approvals

### Approvals


#### Approvals


CSA / UL Recognized / cUL Recognized / GL / GOST / cULus Recognized

#### Ex Approvals

#### Approvals submitted

## Approval details

CSA 			
	B	C	D
mm <sup>2</sup> /AWG/kcmil	24-16	24-16	24-16
Nominal current I <sub>N</sub>	10 A	10 A	5 A
Nominal voltage U <sub>N</sub>	300 V	300 V	600 V

UL Recognized 			
	B	C	D
mm <sup>2</sup> /AWG/kcmil	24-16	24-16	24-16
Nominal current I <sub>N</sub>	10 A	10 A	5 A

# Plug - QP 1,5/ 1-L - 3051014

## Approvals

		B	C	D
Nominal voltage UN	600 V	300 V	300 V	600 V

cUL Recognized

		B	C	D
mm <sup>2</sup> /AWG/kcmil	24-12	24-12	24-12	24-12
Nominal current IN	10 A	10 A	10 A	5 A
Nominal voltage UN	600 V	300 V	300 V	600 V

GL

GOST

cULus Recognized

## Accessories

### Accessories

End cover

Spacer plate - DP PS-5 - 3036725



Spacer plate, Color: red

### Insulating sleeve

Insulating sleeve - MPS-IH WH - 0201663



Insulating sleeve, Color: white

## Plug - QP 1,5/ 1-L - 3051014

### Accessories

Insulating sleeve - MPS-IH RD - 0201676



Insulating sleeve, Color: red

---

Insulating sleeve - MPS-IH BU - 0201689



Insulating sleeve, Color: blue

---

Insulating sleeve - MPS-IH YE - 0201692



Insulating sleeve, Color: yellow

---

Insulating sleeve - MPS-IH GN - 0201702



Insulating sleeve, Color: green

---

Insulating sleeve - MPS-IH GY - 0201728



Insulating sleeve, Color: gray

---

## Plug - QP 1,5/ 1-L - 3051014

### Accessories

Insulating sleeve - MPS-IH BK - 0201731



Insulating sleeve, Color: black

---

### Screwdriver tools

Screwdriver - SZF 1-0,6X3,5 - 1204517



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

---

### Test plug terminal block

Reducing plug - RPS - 0201647



Reducing plug, For test plugs, Color: gray

---

Test plugs - MPS-MT - 0201744



Test plugs, Color: silver

---

Test plugs - PS-5 - 3030983



Test plugs, Color: red

# Plug - QP 1,5/ 1-L - 3051014

## Accessories

Test plugs - PS-5/2,3MM RD - 3038723



Test plugs, Color: red

---

## Drawings

Circuit diagram



Schematic diagram

