



## General Information

Extended Product Type:	SKT200-180X-100
Product ID:	7TCA300140R0001
EAN:	5415022210101
Catalog Description:	UV BLACK TIE 180N 200MM DISTRI PACK
Long Description:	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH- 2 Plenum, Length of 200mm (7.87 Inches), Width of 3.6mm (0.142 Inches), Thickness of 1.2mm (0.047 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds)



## Categories

Products » Low Voltage Products and Systems » Protection, Connection & Wire Management » Wire Management and Connectivity » Cable Ties

## Ordering

EAN:	5415022210101
Minimum Order Quantity:	100 piece
Customs Tariff Number:	3926909995

## Dimensions

Product Net Width:	109.982 mm
Product Net Height:	24.892 mm
Product Net Depth:	320.04 mm
Product Net Weight:	0.12 kg

## Container Information

Package Level 1 Units:	100 piece
Package Level 1 Width:	109.982 mm
Package Level 1 Height:	24.892 mm
Package Level 1 Length:	320.04 mm
Package Level 2 Units:	20000 piece
Package Level 2 Width:	379.984 mm
Package Level 2 Height:	359.918 mm
Package Level 2 Length:	569.976 mm

## Additional Information

Product Main Type:	GENERAL PURPOSE CABLE TIES AND ACCESSORIES
Product Name:	OTHER PLASTIC ITEM
UPC:	753554016378

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	SKT200-180X-100
------------------------------------	-----------------

## Classifications

UNSPSC:	39121703
---------	----------