

Cable - CABLE-D37SUB/B/B/1000/KONFEK/S - 2900762

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Assembled, shielded round cable, with 37-pos. D-SUB socket strip on both sides; cable length 10 m



Key commercial data

Packing unit	1 pc
GTIN	
Weight per Piece (excluding packing)	2110.7 g
Custom tariff number	85444290
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

General

Nominal voltage U_N	125 V AC/DC
Max. current carrying capacity per path	2 A
Max. conductor resistance	$\leq 0.09 \Omega/m$
Length of cable	10 m
Single wire, cross section	0.25 mm ²
AWG	24
External diameter	12 mm
Shielding	yes
	Tinned copper-braided shield, approx. 85% covering
Insertion/withdrawal cycles	> 200

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Flame resistance	IEC 60332-1

Connector, module side

Cable - CABLE-D37SUB/B/B/1000/KONFEK/S - 2900762

Technical data

Connector, module side

Number of positions	37
Connectors	D-SUB socket strip
Number of plugs	1

Connector, controller side

Number of positions	37
Connectors	D-SUB socket strip
Number of plugs	1

Classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27249205

ETIM

ETIM 2.0	EC000237
ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC000237

UNSPSC

UNSPSC 6.01	26121620
UNSPSC 7.0901	26121620
UNSPSC 11	26121620
UNSPSC 12.01	26121620
UNSPSC 13.2	26121620

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / CSA / EAC / cULus Recognized


Ex Approvals


Cable - CABLE-D37SUB/B/B/1000/KONFEK/S - 2900762

Approvals

Approvals submitted

Approval details

UL Recognized 

cUL Recognized 

CSA 

EAC

cULus Recognized 