

Touch panel - TP 15T - 2985204

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Touch panel with 38.1 cm (15") graphics-capable TFT display, 256 colors, 1024 x 768 pixels, 1 x Ethernet, 2 x USB, and integrated runtime of the Visu+ visualization software.

Why buy this product

- Short startup time
- Easy installation, low installation depth, and compact design
- Display available in sizes from 8.9 cm (3.8") to 38.1 cm (15")
- Visu+ RT and AX OPC server integrated as standard in all devices
- Energy efficient due to LED backlighting



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 117197
Weight per Piece (excluding packing)	4718.0 g
Custom tariff number	84714100
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

External dimension, width	400 mm
External dimension, height	329 mm
External dimension, depth	5 mm
Note regarding external dimension	Dimensions of the front plate
Installation dimension, width	373 mm
Installation dimension, height	302 mm

Touch panel - TP 15T - 2985204

Technical data

Dimensions

Installation dimension, depth	70 mm
-------------------------------	-------

Display

Display	38.1 cm/15" TFT
Resolution	1024 x 768 Pixel (XGA)
Backlighting	LED
Touch screen	Resistive industrial touch screen
Colors	65,536 colors

Computer data

Processor	Xscale® PXA320, 806 MHz
Operating systems	Windows CE 5.0
RAM	128 MB SDRAM
Mass storage	1 GB Flash
Network	1 x Ethernet (10/100 Mbps), RJ45
Interfaces	2x USB Host 1.1, 1x Compact Flash®

General

Mounting type	Installation in front plate
---------------	-----------------------------

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	20 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
Vibration (operation)	DIN EN 60068-2-6
Shock	DIN EN 60068-2-27

Classifications

eCl@ss

eCl@ss 4.0	27330202
eCl@ss 4.1	27330202
eCl@ss 5.0	27242215
eCl@ss 5.1	27242301
eCl@ss 6.0	27242301
eCl@ss 7.0	27242301
eCl@ss 8.0	27242302

ETIM

ETIM 2.0	EC001426
ETIM 3.0	EC001426

Touch panel - TP 15T - 2985204

Classifications

ETIM

ETIM 4.0	EC001426
ETIM 5.0	EC001414

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43211903
UNSPSC 13.2	43201404

Approvals

Approvals


Approvals


UL Listed / cUL Listed / GL / BV / ABS / GL-SW / EAC / GL / cULus Listed

Ex Approvals

Approvals submitted

Approval details

UL Listed 

cUL Listed 
--

GL

BV

ABS

GL-SW

Touch panel - TP 15T - 2985204

Approvals

EAC

GL

cULus Listed 

Accessories

Accessories

Battery module

Battery - HMI BATTERY - 2701383

CMOS battery



Mounting material

Mounting kit - HMI WALL MOUNTING KIT - 2701380

HMI mounting kit for panel installation. The mounting kit includes 2 spring clips.



Mounting kit - HMI SCB MOUNTING KIT 4 - 2701384

HMI mounting kit for installation on a front plate. The mounting kit includes 4 x mounting brackets, 4 x screw threads, and a hexagonal wrench.



Mounting kit - HMI SCB MOUNTING KIT 6 - 2701385

HMI mounting kit for installation on a front plate. The mounting kit includes 6 x mounting brackets, 6 x screw threads, and a hexagonal wrench.



Touch panel - TP 15T - 2985204

Accessories

Mounting kit - HMI SCB MOUNTING KIT 8 - 2701387



HMI mounting kit for installation on a front plate. The mounting kit includes 8 x mounting brackets, 8 x screw threads, and a hexagonal wrench.

Operating stylus

Touch pen - TOUCH PEN - 2701379



Touch pen for HMIs, silver coated. Delivery includes self-adhesive pen holder.

Parameterization memory

Memory - CF FLASH 256MB - 2988780



Program and configuration memory, plug-in, 256 MB

Protective foil

Protective foil - 15,1" DISPLAY PROTECTIVE FOIL - 2701378



Protective film set comprising 10 pieces of film for a 15.1" display. Including a squeegee to apply film and instructions.

Storage medium

USB memory stick - 2 GB USB STICK - 2701382



USB memory stick, 2 GB.

Touch panel - TP 15T - 2985204

Accessories

Phoenix Contact 2015 © - all rights reserved
<http://www.phoenixcontact.com>