


**APPLICATION**

Triple protected highly flexible PVC insulated and sheathed power cable for exceptional mechanical and electrical protection, generally in accordance with VDE0250

**CONSTRUCTION**



<b>1. Conductor</b>		
Material		Stranded bare copper
Dimensions		30x0.25 mm (1.50 mm <sup>2</sup> )
<b>2. Insulation</b>		
Material		PVC
Diameter		2.80 ± 0.05 mm
<b>3. Filler</b>		
Material		PVC
Diameter		3.00 mm
<b>4. Stranding</b>		
Lay up		6 cores stranded
Colours		black numbered and yellow/green
<b>5. Bedding</b>		
Material		PVC
Diameter		9.30 ± 0.20 mm
Nominal wall		0.45 mm
<b>6. Armour</b>		
Material		Galvanized steel wire
Diameter		10.38 mm
Coverage		64 %
<b>7. Jacket</b>		
Material		PVC
Diameter		12.58 ± 0.30 mm
Nominal wall		1.10 mm

**REQUIREMENTS AND TEST METHODS****Electrical:**

Voltage rating conductor to earth	300 V RMS
Voltage rating conductor to conductor	500 V RMS
Maximum resistance conductor @ 20°C	13.3 Ω/km
Maximum continuous current per conductor @ 25°C	0.7 x 16 A

**Mechanical and physical:**

Temperature range processing	-5 to +70 °C
Temperature range operating (moving installation)	-5 to +70 °C
Temperature range operating (fixed installation)	-30 to +70 °C
Temperature range storage	-30 to +70 °C
Nominal weight per 100m	25.1 kg
Maximum pulling tension	630 N
Minimum bending radius	10 x D



Belden declares this product to be in compliance with the environmental regulations EU RoHS (Directive 2002/95/EC, 27 January 2003); this is valid for all material produced after the RoHS compliant date for this product.