



ENGLISH

Datasheet

RS Pro Steel Abrasive End Brush, 12000rpm, 10mm Diameter

RS Stock No: **374-474**



Product Details

RS Pro abrasive end brush with steel bristle, has a diameter of 10 mm and shaft diameter of 6 mm. It is perfect for cleaning or deburring hard to reach areas and is available in mild steel wire or stainless steel wire. The steel wire version is identified by green mark on cup section.

Features and Benefits

- Stainless steel bristle construction
- 12000 rpm maximum safe speed
- Shank fixing type
- 27 mm long bristle



ENGLISH

Specifications:

Bristle Material	Steel
Fixing Type	Shank
Bristle Length	27 mm
Diameter	10 mm
Fixing Size	6 mm
Maximum Safe Speed	7000 rpm
Number of Pieces	6
Suitable For	Roughening, Deburring, Planning, Edge Honing, Structuring, Descaling/Paint Stripping & Weld Seams
Type	121 P/L

End brushes
crimped wire



Sharp shape, high stability.



End brushes
crimped wire



Flat shape, high form stability.



USAGE

	0,15	0,20	0,25/0,27	0,30	0,35	0,40	0,50
roughening	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
planing	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
deburring	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
edge honing	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
structuring	<input type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
descaling/paint stripping	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
weld seams	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>

TRIM AND MATERIAL

Products available with:

	Steel	Cast steel	Stainless steel	Non-ferrous metal	Aluminium	Soft wood	Hard wood
Steel wire crimped	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
Stainless steel	<input type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>

Item	Ø	T	L	Type	max RPM	Type
374-503	25	35	50	103 P	12000	Sharp
374-862	25	35	50	103 P	12000	Sharp
374-496	19	31	51	102 P	12000	Sharp
374-856	19	31	51	102 P	12000	Sharp
374-480	12	30	61	124 P	12000	Sharp
374-474	10	27	125	121 P/L	12000	Sharp
374-519	28	24	51	112	12000	Flat
374-525	28	32	51	113	12000	Flat